

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265202

Luminaire Tested: P3AS13R559730DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265202
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-14)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559730DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1124.0 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265202
CATALOG NUMBER: P3AS13R559730DE010 E3D1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1265202

CATALOG NUMBER: P3AS13R559730DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95				95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89				89
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84				84
4	100	93	88	84	98	92	87	84	90	86	83	88	84	82	86	83	81	79				79
5	95	88	83	79	94	87	82	78	85	81	78	84	80	77	82	79	76	75				75
6	91	83	78	74	90	82	77	74	81	76	73	80	76	73	78	75	72	71				71
7	87	79	73	70	86	78	73	69	77	72	69	76	72	69	75	71	68	67				67
8	83	75	69	66	82	74	69	66	73	69	65	72	68	65	71	68	65	63				63
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60				60
10	77	68	62	59	76	67	62	59	67	62	59	66	62	59	65	61	58	57				57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	325939
5°	314417
10°	325645
15°	321069
20°	297153
25°	240304
30°	144022
35°	48800
40°	13454
45°	5954
50°	1740
55°	344
60°	175
65°	208
70°	256
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5954 cd/sqm



TEST NUMBER: P1265202
 CATALOG NUMBER: P3AS13R559730DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	12.3
10°-20°	393.8	35.0
20°-30°	437.7	38.9
30°-40°	136.3	12.1
40°-50°	16.4	1.5
50°-60°	1.3	0.1
60°-70°	0.4	0.0
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	969.6	86.3
0°-40°	1105.9	98.4
0°-60°	1123.5	100.0
0°-90°	1124.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1124.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1486	
5°	1428	138
15°	1414	394
25°	993	438
35°	182	136
45°	19	16
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1265202
CATALOG NUMBER: P3AS13R559730DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1486.4
1°	1480.9
2°	1466.4
3°	1448.4
4°	1432.2
5°	1428.4
6°	1432.6
7°	1441.6
8°	1451.9
9°	1460.0
10°	1462.5
11°	1460.8
12°	1454.0
13°	1443.3
14°	1430.9
15°	1414.3
16°	1395.1
17°	1370.7
18°	1343.4
19°	1310.5
20°	1273.4
21°	1231.1
22°	1181.1
23°	1126.0
24°	1062.8
25°	993.2
26°	916.8
27°	835.7
28°	749.0
29°	659.7
30°	568.8
31°	477.4
32°	388.2
32.5°	348.4
33°	307.5
34°	237.8
35°	182.3
36°	138.8
37°	102.9
37.5°	88.0
38°	76.4
39°	58.1
40°	47.0
42.5°	29.9
45°	19.2



TEST NUMBER: P1265202
CATALOG NUMBER: P3AS13R559730DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	11.5
50°	5.1
52.5°	1.7
55°	0.9
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.4
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)