

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265215

Luminaire Tested: P3AS13R559730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R559730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 311.0 lumens
Efficiency: N/A
Efficacy: 21.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265215

CATALOG NUMBER: P3AS13R559730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265215

CATALOG NUMBER: P3AS13R559730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		97
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	96	88	82	77	94	87	81	77	84	80	76		82	78	75		80
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		68
8	78	68	62	57	76	67	61	57	66	61	57		65	60	57		64
9	74	64	58	54	73	63	58	54	62	57	53		62	57	53		61
10	70	60	55	51	69	60	54	50	59	54	50		58	54	50		58

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	84598
5°	82478
10°	76685
15°	68286
20°	58035
25°	46817
30°	35702
35°	25404
40°	16746
45°	9924
50°	5833
55°	3594
60°	3201
65°	2906
70°	2436
75°	2203
80°	2147
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9924 cd/sqm

TEST NUMBER: P1265215

CATALOG NUMBER: P3AS13R559730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.8	11.2
10°-20°	83.4	26.8
20°-30°	88.3	28.4
30°-40°	59.7	19.2
40°-50°	26.1	8.4
50°-60°	9.4	3.0
60°-70°	5.5	1.8
70°-80°	2.9	0.9
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	206.5	66.4
0°-40°	266.2	85.6
0°-60°	301.7	97.0
0°-90°	311.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	311.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	386	
5°	375	35
15°	301	83
25°	194	88
35°	95	60
45°	32	26
55°	9	9
65°	6	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1265215

CATALOG NUMBER: P3AS13R559730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	385.8
2.5°	382.8
5°	374.7
7.5°	361.5
10°	344.4
12.5°	323.9
15°	300.8
17.5°	275.2
20°	248.7
22.5°	220.9
25°	193.5
27.5°	166.6
30°	141.0
32.5°	116.6
35°	94.9
37.5°	75.2
40°	58.5
42.5°	44.0
45°	32.0
47.5°	23.5
50°	17.1
52.5°	12.0
55°	9.4
57.5°	8.5
60°	7.3
62.5°	6.4
65°	5.6
67.5°	4.7
70°	3.8
72.5°	3.4
75°	2.6
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)