

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265802

Luminaire Tested: P3AS20R309730D010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265802
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309730D010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1179.0 lumens
Efficiency: N/A
Efficacy: 40.9 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265802

CATALOG NUMBER: P3AS20R309730D010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1265802

CATALOG NUMBER: P3AS20R309730D010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94
2	104	98	93	88	102	96	91	87	93	89	85		90	86	83		87
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64
7	76	65	57	52	74	64	57	52	62	56	52		61	56	52		60
8	71	60	53	48	70	60	53	48	58	52	48		57	52	48		56
9	68	57	50	45	66	56	49	45	55	49	45		54	49	45		53
10	64	53	47	42	63	53	46	42	52	46	42		51	46	42		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	290525
5°	277679
10°	239519
15°	198526
20°	162741
25°	131185
30°	105738
35°	86625
40°	71963
45°	61030
50°	52194
55°	45150
60°	40260
65°	35179
70°	30839
75°	25925
80°	19321
85°	11070

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 61030 cd/sqm

TEST NUMBER: P1265802

CATALOG NUMBER: P3AS20R309730D010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.4	9.7
10°-20°	243.9	20.7
20°-30°	250.0	21.2
30°-40°	204.3	17.3
40°-50°	152.8	13.0
50°-60°	107.3	9.1
60°-70°	67.5	5.7
70°-80°	32.6	2.8
80°-90°	6.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	608.2	51.6
0°-40°	812.5	68.9
0°-60°	1072.7	91.0
0°-90°	1179.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1179.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1325	
5°	1262	114
15°	874	244
25°	542	250
35°	324	204
45°	197	153
55°	118	107
65°	68	68
75°	31	33
85°	4	6
90°	0	

TEST NUMBER: P1265802

CATALOG NUMBER: P3AS20R309730D010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1324.9
2.5°	1311.8
5°	1261.5
7.5°	1178.4
10°	1075.7
12.5°	975.1
15°	874.5
17.5°	782.7
20°	697.4
22.5°	616.5
25°	542.2
27.5°	476.6
30°	417.6
32.5°	369.5
35°	323.6
37.5°	286.4
40°	251.4
42.5°	223.0
45°	196.8
47.5°	172.7
50°	153.0
52.5°	135.5
55°	118.1
57.5°	104.9
60°	91.8
62.5°	78.7
65°	67.8
67.5°	56.8
70°	48.1
72.5°	39.4
75°	30.6
77.5°	21.9
80°	15.3
82.5°	8.7
85°	4.4
87.5°	2.2
90°	0.0

(END OF REPORT)