

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265243

Luminaire Tested: P3AS13R609730DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265243
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609730DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 718.0 lumens
Efficiency: N/A
Efficacy: 49.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265243

CATALOG NUMBER: P3AS13R609730DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265243

CATALOG NUMBER: P3AS13R609730DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127446
5°	126018
10°	121663
15°	114938
20°	105943
25°	95933
30°	85178
35°	72786
40°	57880
45°	40810
50°	24392
55°	12310
60°	11841
65°	10844
70°	10066
75°	9574
80°	8840
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 40810 cd/sqm

TEST NUMBER: P1265243

CATALOG NUMBER: P3AS13R609730DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.8	7.5
10°-20°	141.5	19.7
20°-30°	181.7	25.3
30°-40°	168.5	23.5
40°-50°	102.6	14.3
50°-60°	34.2	4.8
60°-70°	20.8	2.9
70°-80°	11.7	1.6
80°-90°	3.3	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	377.0	52.5
0°-40°	545.5	76.0
0°-60°	682.2	95.0
0°-90°	718.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	718.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	581	
5°	572	54
15°	506	141
25°	396	182
35°	272	168
45°	132	103
55°	32	34
65°	21	21
75°	11	12
85°	3	3
90°	0	

TEST NUMBER: P1265243

CATALOG NUMBER: P3AS13R609730DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	581.2
2.5°	578.6
5°	572.5
7.5°	561.2
10°	546.4
12.5°	528.1
15°	506.3
17.5°	481.0
20°	454.0
22.5°	425.3
25°	396.5
27.5°	366.9
30°	336.4
32.5°	305.9
35°	271.9
37.5°	236.2
40°	202.2
42.5°	166.4
45°	131.6
47.5°	102.0
50°	71.5
52.5°	42.7
55°	32.2
57.5°	29.6
60°	27.0
62.5°	23.5
65°	20.9
67.5°	18.3
70°	15.7
72.5°	13.1
75°	11.3
77.5°	8.7
80°	7.0
82.5°	4.4
85°	2.6
87.5°	1.7
90°	0.0

(END OF REPORT)