

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265249

Luminaire Tested: P3AS13R609730DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265249
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609730DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 634.0 lumens
Efficiency: N/A
Efficacy: 43.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265249

CATALOG NUMBER: P3AS13R609730DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265249

CATALOG NUMBER: P3AS13R609730DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	160667
5°	157076
10°	147047
15°	131919
20°	113457
25°	93804
30°	74113
35°	55038
40°	37900
45°	23785
50°	13066
55°	7646
60°	6885
65°	5863
70°	5001
75°	5168
80°	4420
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23785 cd/sqm

TEST NUMBER: P1265249

CATALOG NUMBER: P3AS13R609730DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.4	10.5
10°-20°	161.4	25.5
20°-30°	177.0	27.9
30°-40°	129.0	20.3
40°-50°	60.9	9.6
50°-60°	19.9	3.1
60°-70°	11.3	1.8
70°-80°	6.1	1.0
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	404.9	63.9
0°-40°	533.8	84.2
0°-60°	614.7	97.0
0°-90°	634.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	634.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	733	
5°	714	66
15°	581	161
25°	388	177
35°	206	129
45°	77	61
55°	20	20
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1265249

CATALOG NUMBER: P3AS13R609730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	732.7
2.5°	728.4
5°	713.6
7.5°	690.9
10°	660.4
12.5°	623.8
15°	581.1
17.5°	535.0
20°	486.2
22.5°	436.5
25°	387.7
27.5°	338.9
30°	292.7
32.5°	248.3
35°	205.6
37.5°	167.3
40°	132.4
42.5°	101.9
45°	76.7
47.5°	55.8
50°	38.3
52.5°	25.3
55°	20.0
57.5°	17.4
60°	15.7
62.5°	13.1
65°	11.3
67.5°	9.6
70°	7.8
72.5°	7.0
75°	6.1
77.5°	4.4
80°	3.5
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)