

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265842

Luminaire Tested: P3AS20R409730D010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265842
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409730D010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2122.0 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265842

CATALOG NUMBER: P3AS20R409730D010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265842

CATALOG NUMBER: P3AS20R409730D010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		93
4	103	97	93	90	101	96	92	89	94	91	88		92	89	87		90
5	99	93	89	85	98	92	88	85	91	87	84		89	86	84		88
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		85
7	93	86	81	78	92	85	81	78	84	80	77		83	80	77		82
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		79
9	87	80	75	72	86	79	75	72	78	75	72		78	74	72		77
10	84	77	72	70	83	77	72	69	76	72	69		75	72	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1081624
5°	1073825
10°	1045717
15°	934103
20°	619391
25°	232030
30°	62060
35°	24253
40°	8731
45°	4155
50°	1262
55°	573
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4155 cd/sqm

TEST NUMBER: P1265842

CATALOG NUMBER: P3AS20R409730D010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	460.4	21.7
10°-20°	1090.3	51.4
20°-30°	494.4	23.3
30°-40°	64.1	3.0
40°-50°	11.1	0.5
50°-60°	1.3	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2045.1	96.4
0°-40°	2109.1	99.4
0°-60°	2121.6	100.0
0°-90°	2122.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2122.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4933	
5°	4878	460
15°	4115	1090
25°	959	494
35°	91	64
45°	13	11
55°	2	1
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1265842

CATALOG NUMBER: P3AS20R409730D010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4932.6
1°	4929.7
2°	4922.2
3°	4911.1
4°	4897.0
5°	4878.4
6°	4856.9
7°	4830.1
8°	4797.4
9°	4752.9
10°	4696.4
11°	4630.3
12°	4541.9
13°	4432.7
14°	4290.1
15°	4114.7
16°	3891.1
17°	3636.3
18°	3330.3
19°	3007.1
20°	2654.3
21°	2301.4
22°	1953.7
23°	1607.6
24°	1267.3
25°	959.0
26°	710.2
27°	520.0
28°	390.7
29°	303.8
30°	245.1
31°	202.8
32°	169.4
32.5°	154.5
33°	139.7
34°	113.7
35°	90.6
36°	71.3
37°	56.5
37.5°	50.5
38°	44.6
39°	37.1
40°	30.5
42.5°	20.1
45°	13.4



TEST NUMBER: P1265842

CATALOG NUMBER: P3AS20R409730D010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	8.2
50°	3.7
52.5°	1.5
55°	1.5
57.5°	0.7
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)