

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265258

Luminaire Tested: P3AS13R659730DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659730DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1078.0 lumens
Efficiency: N/A
Efficacy: 73.8 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265258
CATALOG NUMBER: P3AS13R659730DE010 E3D1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1265258
 CATALOG NUMBER: P3AS13R659730DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				94
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87				87
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81				81
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75				75
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70				70
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66				66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62				62
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58				58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54				54
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	263444
5°	247941
10°	244796
15°	240478
20°	227053
25°	210738
30°	163797
35°	94763
40°	38186
45°	17583
50°	6857
55°	2676
60°	2281
65°	2283
70°	2244
75°	2203
80°	2147
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17583 cd/sqm



TEST NUMBER: P1265258
 CATALOG NUMBER: P3AS13R659730DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.1	9.9
10°-20°	295.8	27.4
20°-30°	387.2	35.9
30°-40°	224.3	20.8
40°-50°	48.0	4.5
50°-60°	7.8	0.7
60°-70°	4.3	0.4
70°-80°	2.5	0.2
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	790.1	73.3
0°-40°	1014.4	94.1
0°-60°	1070.3	99.3
0°-90°	1078.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1078.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1201	
5°	1126	107
15°	1059	296
25°	871	387
35°	354	224
45°	57	48
55°	7	8
65°	4	4
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1265258
CATALOG NUMBER: P3AS13R659730DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1201.4
2.5°	1167.4
5°	1126.4
7.5°	1109.8
10°	1099.4
12.5°	1084.6
15°	1059.3
17.5°	1020.0
20°	973.0
22.5°	928.5
25°	871.0
27.5°	774.2
30°	646.9
32.5°	501.3
35°	354.0
37.5°	224.1
40°	133.4
42.5°	83.7
45°	56.7
47.5°	36.6
50°	20.1
52.5°	9.6
55°	7.0
57.5°	6.1
60°	5.2
62.5°	5.2
65°	4.4
67.5°	3.5
70°	3.5
72.5°	2.6
75°	2.6
77.5°	1.7
80°	1.7
82.5°	0.9
85°	0.9
87.5°	0.9
90°	0.0

(END OF REPORT)