

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265261

Luminaire Tested: P3AS13R659730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265261
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 428.0 lumens
Efficiency: N/A
Efficacy: 29.3 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265261
CATALOG NUMBER: P3AS13R659730DE010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1265261
 CATALOG NUMBER: P3AS13R659730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85			85
3	101	95	89	85	99	93	88	84	90	86	83	88	85	82	86	83	80	79			79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	74	73			73
5	91	82	76	71	89	81	75	71	79	74	70	77	73	70	76	72	69	68			68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	67	64	63			63
7	82	72	66	61	80	71	65	61	70	64	61	69	64	60	67	63	60	58			58
8	77	67	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55			55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51			51
10	70	60	54	50	69	59	54	50	59	53	50	58	53	50	57	53	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	100935
5°	99714
10°	95946
15°	89876
20°	80834
25°	68641
30°	53679
35°	38253
40°	25047
45°	15474
50°	7846
55°	2791
60°	2412
65°	2439
70°	2180
75°	2203
80°	2147
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 15474 cd/sqm



TEST NUMBER: P1265261
 CATALOG NUMBER: P3AS13R659730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.5	9.9
10°-20°	110.2	25.7
20°-30°	128.8	30.1
30°-40°	90.0	21.0
40°-50°	39.6	9.3
50°-60°	8.8	2.1
60°-70°	4.5	1.0
70°-80°	2.7	0.6
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	281.5	65.8
0°-40°	371.5	86.8
0°-60°	419.9	98.1
0°-90°	428.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	428.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	460	
5°	453	43
15°	396	110
25°	284	129
35°	143	90
45°	50	40
55°	7	9
65°	5	4
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1265261
CATALOG NUMBER: P3AS13R659730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	460.3
2.5°	458.6
5°	453.0
7.5°	443.7
10°	430.9
12.5°	415.1
15°	395.9
17.5°	372.4
20°	346.4
22.5°	317.0
25°	283.7
27.5°	248.7
30°	212.0
32.5°	176.6
35°	142.9
37.5°	113.5
40°	87.5
42.5°	66.1
45°	49.9
47.5°	36.7
50°	23.0
52.5°	11.9
55°	7.3
57.5°	6.4
60°	5.5
62.5°	5.1
65°	4.7
67.5°	3.8
70°	3.4
72.5°	3.0
75°	2.6
77.5°	2.1
80°	1.7
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)