

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265892

Luminaire Tested: P3AS20R509730D010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265892
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509730D010 E3D1H
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2105.0 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265892

CATALOG NUMBER: P3AS20R509730D010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1265892

CATALOG NUMBER: P3AS20R509730D010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	735621
5°	716023
10°	683287
15°	618596
20°	535173
25°	438993
30°	252165
35°	78327
40°	21039
45°	7381
50°	1774
55°	573
60°	307
65°	363
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7381 cd/sqm

TEST NUMBER: P1265892

CATALOG NUMBER: P3AS20R509730D010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	304.7	14.5
10°-20°	755.0	35.9
20°-30°	793.6	37.7
30°-40°	227.1	10.8
40°-50°	22.2	1.1
50°-60°	1.8	0.1
60°-70°	0.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1853.3	88.0
0°-40°	2080.4	98.8
0°-60°	2104.4	100.0
0°-90°	2105.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2105.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3355	
5°	3253	305
15°	2725	755
25°	1814	794
35°	293	227
45°	24	22
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1265892

CATALOG NUMBER: P3AS20R509730D010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	3354.7
1°	3349.5
2°	3334.6
3°	3313.1
4°	3284.1
5°	3252.9
6°	3219.5
7°	3183.9
8°	3150.4
9°	3111.8
10°	3068.7
11°	3019.0
12°	2961.8
13°	2890.5
14°	2813.3
15°	2724.9
16°	2631.3
17°	2540.7
18°	2447.9
19°	2366.2
20°	2293.4
21°	2223.6
22°	2144.1
23°	2052.8
24°	1945.8
25°	1814.4
26°	1671.8
27°	1512.8
28°	1354.6
29°	1183.8
30°	995.9
31°	819.9
32°	658.0
32.5°	587.5
33°	516.2
34°	395.8
35°	292.6
36°	214.6
37°	159.7
37.5°	138.1
38°	119.6
39°	92.8
40°	73.5
42.5°	41.6
45°	23.8

TEST NUMBER: P1265892

CATALOG NUMBER: P3AS20R509730D010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	13.4
50°	5.2
52.5°	2.2
55°	1.5
57.5°	1.5
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)