

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265266

Luminaire Tested: P3AS13R659730DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265266
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659730DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 874.0 lumens
Efficiency: N/A
Efficacy: 59.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265266

CATALOG NUMBER: P3AS13R659730DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265266

CATALOG NUMBER: P3AS13R659730DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	206124
5°	203631
10°	195899
15°	183520
20°	165074
25°	140161
30°	109637
35°	78113
40°	51124
45°	31600
50°	16034
55°	5658
60°	4956
65°	4981
70°	4488
75°	4406
80°	4420
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31600 cd/sqm

TEST NUMBER: P1265266

CATALOG NUMBER: P3AS13R659730DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.9	9.9
10°-20°	225.0	25.7
20°-30°	263.0	30.1
30°-40°	183.8	21.0
40°-50°	80.9	9.3
50°-60°	18.0	2.1
60°-70°	9.2	1.0
70°-80°	5.5	0.6
80°-90°	1.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.8	65.8
0°-40°	758.6	86.8
0°-60°	857.4	98.1
0°-90°	874.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	874.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	940	
5°	925	87
15°	808	225
25°	579	263
35°	292	184
45°	102	81
55°	15	18
65°	10	9
75°	5	6
85°	2	2
90°	0	

TEST NUMBER: P1265266

CATALOG NUMBER: P3AS13R659730DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	940.0
2.5°	936.5
5°	925.1
7.5°	906.0
10°	879.8
12.5°	847.6
15°	808.4
17.5°	760.5
20°	707.4
22.5°	647.3
25°	579.3
27.5°	507.9
30°	433.0
32.5°	360.7
35°	291.8
37.5°	231.7
40°	178.6
42.5°	135.0
45°	101.9
47.5°	74.9
50°	47.0
52.5°	24.4
55°	14.8
57.5°	13.1
60°	11.3
62.5°	10.5
65°	9.6
67.5°	7.8
70°	7.0
72.5°	6.1
75°	5.2
77.5°	4.4
80°	3.5
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)