

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265272

Luminaire Tested: P3AS13R659730DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265272
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659730DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 686.0 lumens
Efficiency: N/A
Efficacy: 47.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265272

CATALOG NUMBER: P3AS13R659730DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265272

CATALOG NUMBER: P3AS13R659730DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	122074
5°	120427
10°	116386
15°	109762
20°	101252
25°	91917
30°	81405
35°	69279
40°	55103
45°	38919
50°	22583
55°	12310
60°	11446
65°	10377
70°	9489
75°	8896
80°	7703
85°	6542

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 38919 cd/sqm

TEST NUMBER: P1265272

CATALOG NUMBER: P3AS13R659730DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.5	7.5
10°-20°	135.3	19.7
20°-30°	173.9	25.3
30°-40°	160.8	23.4
40°-50°	97.1	14.2
50°-60°	33.1	4.8
60°-70°	19.9	2.9
70°-80°	11.3	1.6
80°-90°	3.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.6	52.6
0°-40°	521.4	76.0
0°-60°	651.6	95.0
0°-90°	686.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	686.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	557	
5°	547	51
15°	484	135
25°	380	174
35°	259	161
45°	126	97
55°	32	33
65°	20	20
75°	10	11
85°	3	3
90°	0	

TEST NUMBER: P1265272

CATALOG NUMBER: P3AS13R659730DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	556.7
2.5°	554.1
5°	547.1
7.5°	536.7
10°	522.7
12.5°	505.3
15°	483.5
17.5°	460.0
20°	433.9
22.5°	406.9
25°	379.9
27.5°	351.1
30°	321.5
32.5°	291.9
35°	258.8
37.5°	226.5
40°	192.5
42.5°	158.6
45°	125.5
47.5°	95.0
50°	66.2
52.5°	41.8
55°	32.2
57.5°	28.8
60°	26.1
62.5°	22.7
65°	20.0
67.5°	17.4
70°	14.8
72.5°	13.1
75°	10.5
77.5°	8.7
80°	6.1
82.5°	4.4
85°	2.6
87.5°	1.7
90°	0.0

(END OF REPORT)