

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265919

Luminaire Tested: P3AS20R559730D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265919
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559730D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2017.0 lumens
Efficiency: N/A
Efficacy: 70.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265919
CATALOG NUMBER: P3AS20R559730D010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1265919
 CATALOG NUMBER: P3AS20R559730D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89			
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84			
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	86	83	80	79			
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70			
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66			
8	83	74	69	65	82	74	69	65	73	68	65	72	67	64	71	67	64	63			
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60			
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	559429
5°	554214
10°	576498
15°	568494
20°	524229
25°	426533
30°	259078
35°	89677
40°	25591
45°	12218
50°	5185
55°	2332
60°	2675
65°	2335
70°	1923
75°	2542
80°	1894
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12218 cd/sqm



TEST NUMBER: P1265919
 CATALOG NUMBER: P3AS20R559730D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.4	12.1
10°-20°	696.0	34.5
20°-30°	775.9	38.5
30°-40°	253.8	12.6
40°-50°	33.5	1.7
50°-60°	7.1	0.4
60°-70°	4.1	0.2
70°-80°	2.6	0.1
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1715.3	85.0
0°-40°	1969.1	97.6
0°-60°	2009.7	99.6
0°-90°	2017.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2017.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2551	
5°	2518	243
15°	2504	696
25°	1763	776
35°	335	254
45°	39	33
55°	6	7
65°	4	4
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P1265919
CATALOG NUMBER: P3AS20R559730D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	2551.2
2.5°	2533.0
5°	2517.8
7.5°	2554.2
10°	2589.1
12.5°	2570.9
15°	2504.2
17.5°	2398.1
20°	2246.5
22.5°	2037.3
25°	1762.9
27.5°	1414.3
30°	1023.2
32.5°	627.6
35°	335.0
37.5°	169.8
40°	89.4
42.5°	57.6
45°	39.4
47.5°	27.3
50°	15.2
52.5°	9.1
55°	6.1
57.5°	6.1
60°	6.1
62.5°	4.5
65°	4.5
67.5°	3.0
70°	3.0
72.5°	3.0
75°	3.0
77.5°	1.5
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)