

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265929

Luminaire Tested: P3AS20R559730D010 E3DL1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265929
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559730D010 E3DL1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 97CRI , E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1652.0 lumens
Efficiency: N/A
Efficacy: 57.4 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265929
CATALOG NUMBER: P3AS20R559730D010 E3DL1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1265929
 CATALOG NUMBER: P3AS20R559730D010 E3DL1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	82	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	68	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	69	63	60	67	63	60	67	62	59	58			
9	76	66	61	57	75	66	60	56	65	60	56	64	59	56	63	59	56	55			
10	73	63	57	53	72	62	57	53	62	57	53	61	56	53	60	56	53	52			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	453626
5°	449019
10°	433637
15°	400820
20°	345877
25°	273185
30°	193777
35°	124959
40°	75055
45°	42299
50°	22754
55°	8105
60°	7324
65°	7057
70°	6796
75°	6439
80°	5683
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 42299 cd/sqm



TEST NUMBER: P1265929
 CATALOG NUMBER: P3AS20R559730D010 E3DL1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.8	11.6
10°-20°	488.2	29.6
20°-30°	511.7	31.0
30°-40°	298.5	18.1
40°-50°	111.7	6.8
50°-60°	26.3	1.6
60°-70°	13.5	0.8
70°-80°	8.0	0.5
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1191.7	72.1
0°-40°	1490.3	90.2
0°-60°	1628.2	98.6
0°-90°	1652.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1652.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2069	
5°	2040	192
15°	1766	488
25°	1129	512
35°	467	299
45°	136	112
55°	21	26
65°	14	13
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1265929
CATALOG NUMBER: P3AS20R559730D010 E3DL1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	2068.7
2.5°	2062.6
5°	2039.9
7.5°	2003.5
10°	1947.5
12.5°	1868.7
15°	1765.6
17.5°	1635.3
20°	1482.2
22.5°	1310.9
25°	1129.1
27.5°	942.7
30°	765.3
32.5°	604.7
35°	466.8
37.5°	354.6
40°	262.2
42.5°	187.9
45°	136.4
47.5°	98.5
50°	66.7
52.5°	37.9
55°	21.2
57.5°	18.2
60°	16.7
62.5°	15.2
65°	13.6
67.5°	12.1
70°	10.6
72.5°	9.1
75°	7.6
77.5°	6.1
80°	4.5
82.5°	3.0
85°	1.5
87.5°	1.5
90°	0.0

(END OF REPORT)