

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265290

Luminaire Tested: P3AS13R709730DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265290
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709730DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 430.0 lumens
Efficiency: N/A
Efficacy: 29.5 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265290

CATALOG NUMBER: P3AS13R709730DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265290

CATALOG NUMBER: P3AS13R709730DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	92	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	83239
5°	82236
10°	79869
15°	76482
20°	71640
25°	65084
30°	56237
35°	44812
40°	32633
45°	21460
50°	10064
55°	3097
60°	2982
65°	2906
70°	2757
75°	2881
80°	2652
85°	2264

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21460 cd/sqm

TEST NUMBER: P1265290

CATALOG NUMBER: P3AS13R709730DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.2	8.2
10°-20°	94.3	21.9
20°-30°	122.6	28.5
30°-40°	104.0	24.2
40°-50°	53.6	12.5
50°-60°	10.3	2.4
60°-70°	5.6	1.3
70°-80°	3.4	0.8
80°-90°	1.0	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	252.0	58.6
0°-40°	356.0	82.8
0°-60°	420.0	97.7
0°-90°	430.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	430.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	380	
5°	374	35
15°	337	94
25°	269	123
35°	167	104
45°	69	54
55°	8	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1265290

CATALOG NUMBER: P3AS13R709730DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	379.6
2.5°	378.3
5°	373.6
7.5°	366.8
10°	358.7
12.5°	348.5
15°	336.9
17.5°	322.8
20°	307.0
22.5°	289.1
25°	269.0
27.5°	246.4
30°	222.1
32.5°	195.1
35°	167.4
37.5°	140.1
40°	114.0
42.5°	89.7
45°	69.2
47.5°	50.8
50°	29.5
52.5°	12.8
55°	8.1
57.5°	7.7
60°	6.8
62.5°	6.4
65°	5.6
67.5°	5.1
70°	4.3
72.5°	3.8
75°	3.4
77.5°	2.6
80°	2.1
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)