

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265298

Luminaire Tested: P3AS13R709730DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265298
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R709730DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 626.0 lumens
Efficiency: N/A
Efficacy: 42.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265298
CATALOG NUMBER: P3AS13R709730DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1265298
 CATALOG NUMBER: P3AS13R709730DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	146830
5°	144133
10°	135914
15°	123361
20°	107903
25°	91021
30°	74518
35°	57822
40°	41363
45°	26204
50°	13066
55°	7990
60°	6885
65°	6330
70°	5578
75°	5168
80°	4420
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 26204 cd/sqm



TEST NUMBER: P1265298
 CATALOG NUMBER: P3AS13R709730DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.1	9.8
10°-20°	151.2	24.2
20°-30°	172.2	27.5
30°-40°	134.7	21.5
40°-50°	66.1	10.6
50°-60°	20.4	3.3
60°-70°	12.0	1.9
70°-80°	6.4	1.0
80°-90°	1.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	384.5	61.4
0°-40°	519.1	82.9
0°-60°	605.6	96.7
0°-90°	626.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	626.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	670	
5°	655	61
15°	543	151
25°	376	172
35°	216	135
45°	84	66
55°	21	20
65°	12	12
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1265298
CATALOG NUMBER: P3AS13R709730DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	669.6
2.5°	666.1
5°	654.8
7.5°	636.5
10°	610.4
12.5°	579.9
15°	543.4
17.5°	504.2
20°	462.4
22.5°	418.8
25°	376.2
27.5°	334.4
30°	294.3
32.5°	254.3
35°	216.0
37.5°	179.4
40°	144.5
42.5°	112.3
45°	84.5
47.5°	59.2
50°	38.3
52.5°	25.3
55°	20.9
57.5°	18.3
60°	15.7
62.5°	13.9
65°	12.2
67.5°	10.4
70°	8.7
72.5°	7.0
75°	6.1
77.5°	5.2
80°	3.5
82.5°	2.6
85°	1.7
87.5°	0.9
90°	0.0

(END OF REPORT)