

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265310

Luminaire Tested: P3AS17R159730DE010 E3D1H

Issue Date: 1/29/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1265310  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R159730DE010 E3D1H  
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3D1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1493.0 lumens  
Efficiency: N/A  
Efficacy: 70.4 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265310  
CATALOG NUMBER: P3AS17R159730DE010 E3D1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1265310  
 CATALOG NUMBER: P3AS17R159730DE010 E3D1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	111	113	112	110	109	108	107	105	104	103	102	101	100	99	98	98	98	98
2	112	109	107	105	110	108	105	103	105	103	101	102	100	99	99	98	97	96	96	96	96
3	110	106	102	100	108	104	102	99	102	100	98	100	98	96	98	96	95	94	94	94	94
4	107	102	99	96	105	101	98	96	99	97	95	98	96	94	96	94	93	92	92	92	92
5	105	100	96	94	103	99	96	93	97	94	92	96	93	92	94	93	91	90	90	90	90
6	102	97	94	91	101	96	93	91	95	92	90	94	92	90	93	91	89	88	88	88	88
7	100	95	91	89	99	94	91	89	93	90	88	92	90	88	91	89	88	87	87	87	87
8	98	93	89	87	97	92	89	87	91	89	87	91	88	86	90	88	86	85	85	85	85
9	96	91	88	85	96	91	87	85	90	87	85	89	87	85	88	86	85	84	84	84	84
10	95	89	86	84	94	89	86	84	88	85	83	88	85	83	87	85	83	82	82	82	82

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2843062
5°	2318330
10°	1135383
15°	347516
20°	147176
25°	66560
30°	25953
35°	11966
40°	3721
45°	1395
50°	580
55°	229
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1395 cd/sqm



TEST NUMBER: P1265310  
 CATALOG NUMBER: P3AS17R159730DE010 E3D1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	819.8	54.9
10°-20°	503.1	33.7
20°-30°	135.1	9.0
30°-40°	29.8	2.0
40°-50°	4.2	0.3
50°-60°	0.8	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1458.0	97.7
0°-40°	1487.7	99.6
0°-60°	1492.7	100.0
0°-90°	1493.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1493.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12965	
5°	10532	820
15°	1531	503
25°	275	135
35°	45	30
45°	4	4
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1265310  
CATALOG NUMBER: P3AS17R159730DE010 E3D1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	12965.4
1°	12884.4
2°	12624.6
3°	12156.4
4°	11451.6
5°	10532.2
6°	9492.2
7°	8333.9
8°	7269.6
9°	6141.3
10°	5099.1
11°	4067.6
12°	3129.5
13°	2407.2
14°	1905.6
15°	1530.8
17.5°	948.8
20°	630.7
22.5°	424.6
25°	275.1
27.5°	163.0
30°	102.5
32.5°	69.1
35°	44.7
37.5°	24.9
40°	13.0
42.5°	7.4
45°	4.5
47.5°	2.8
50°	1.7
52.5°	1.1
55°	0.6
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1265310  
CATALOG NUMBER: P3AS17R159730DE010 E3D1H

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)