

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265323

Luminaire Tested: P3AS17R159730DE010 E3DLD1LI

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1265323  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R159730DE010 E3DLD1LI  
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 911.0 lumens  
Efficiency: N/A  
Efficacy: 43.0 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265323

CATALOG NUMBER: P3AS17R159730DE010 E3DLD1LI

### Luminous Intensity Polar Plot



TEST NUMBER: P1265323

CATALOG NUMBER: P3AS17R159730DE010 E3DLD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 113 | 109 | 106 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 95  | 93  | 91  |    |    |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 95  | 91  | 95  | 92  | 89  | 92  | 90  | 87  | 90  | 87  | 85  | 83  |    |    |
| 3   | 100 | 93  | 87  | 83  | 98  | 91  | 86  | 82  | 89  | 84  | 81  | 86  | 82  | 79  | 84  | 81  | 78  | 76  |    |    |
| 4   | 94  | 86  | 80  | 75  | 92  | 85  | 79  | 74  | 82  | 77  | 73  | 80  | 76  | 73  | 78  | 75  | 72  | 70  |    |    |
| 5   | 89  | 80  | 73  | 68  | 87  | 79  | 73  | 68  | 77  | 72  | 67  | 75  | 70  | 67  | 74  | 69  | 66  | 65  |    |    |
| 6   | 84  | 74  | 68  | 63  | 83  | 73  | 67  | 63  | 72  | 66  | 62  | 70  | 66  | 62  | 69  | 65  | 61  | 60  |    |    |
| 7   | 80  | 69  | 63  | 58  | 78  | 69  | 63  | 58  | 67  | 62  | 58  | 66  | 61  | 57  | 65  | 61  | 57  | 56  |    |    |
| 8   | 76  | 65  | 59  | 54  | 74  | 65  | 58  | 54  | 63  | 58  | 54  | 62  | 57  | 54  | 61  | 57  | 53  | 52  |    |    |
| 9   | 72  | 61  | 55  | 51  | 71  | 61  | 55  | 51  | 60  | 54  | 50  | 59  | 54  | 50  | 58  | 53  | 50  | 49  |    |    |
| 10  | 68  | 58  | 52  | 48  | 67  | 57  | 51  | 47  | 57  | 51  | 47  | 56  | 51  | 47  | 55  | 50  | 47  | 46  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 229784 |
| 5°  | 223552 |
| 10° | 204294 |
| 15° | 178934 |
| 20° | 153500 |
| 25° | 128161 |
| 30° | 102573 |
| 35° | 76935  |
| 40° | 55819  |
| 45° | 36500  |
| 50° | 22822  |
| 55° | 15445  |
| 60° | 13683  |
| 65° | 12556  |
| 70° | 11861  |
| 75° | 10760  |
| 80° | 10229  |
| 85° | 8806   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 36500 cd/sqm

TEST NUMBER: P1265323

CATALOG NUMBER: P3AS17R159730DE010 E3DLD1LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 93.7   | 10.3      |
| 10°-20°   | 219.6  | 24.1      |
| 20°-30°   | 242.0  | 26.6      |
| 30°-40°   | 181.2  | 19.9      |
| 40°-50°   | 93.9   | 10.3      |
| 50°-60°   | 38.9   | 4.3       |
| 60°-70°   | 24.1   | 2.6       |
| 70°-80°   | 13.6   | 1.5       |
| 80°-90°   | 4.0    | 0.4       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 555.3  | 61.0      |
| 0°-40°    | 736.5  | 80.8      |
| 0°-60°    | 869.4  | 95.4      |
| 0°-90°    | 911.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 911.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1048 |      |
| 5°  | 1016 | 94   |
| 15° | 788  | 220  |
| 25° | 530  | 242  |
| 35° | 287  | 181  |
| 45° | 118  | 94   |
| 55° | 40   | 39   |
| 65° | 24   | 24   |
| 75° | 13   | 14   |
| 85° | 4    | 4    |
| 90° | 0    |      |

TEST NUMBER: P1265323

CATALOG NUMBER: P3AS17R159730DE010 E3DLD1LI

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1047.9 |
| 1°    | 1049.1 |
| 2°    | 1045.6 |
| 3°    | 1038.7 |
| 4°    | 1028.3 |
| 5°    | 1015.6 |
| 6°    | 999.4  |
| 7°    | 982.1  |
| 8°    | 961.4  |
| 9°    | 939.4  |
| 10°   | 917.5  |
| 12.5° | 854.0  |
| 15°   | 788.2  |
| 17.5° | 722.5  |
| 20°   | 657.8  |
| 22.5° | 592.0  |
| 25°   | 529.7  |
| 27.5° | 467.4  |
| 30°   | 405.1  |
| 32.5° | 343.9  |
| 35°   | 287.4  |
| 37.5° | 238.9  |
| 40°   | 195.0  |
| 42.5° | 154.6  |
| 45°   | 117.7  |
| 47.5° | 88.9   |
| 50°   | 66.9   |
| 52.5° | 49.6   |
| 55°   | 40.4   |
| 57.5° | 35.8   |
| 60°   | 31.2   |
| 62.5° | 27.7   |
| 65°   | 24.2   |
| 67.5° | 20.8   |
| 70°   | 18.5   |
| 72.5° | 15.0   |
| 75°   | 12.7   |
| 77.5° | 10.4   |
| 80°   | 8.1    |
| 82.5° | 5.8    |
| 85°   | 3.5    |
| 87.5° | 1.2    |
| 90°   | 0.0    |

(END OF REPORT)