

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265327

Luminaire Tested: P3AS17R159730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265327
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 348.0 lumens
Efficiency: N/A
Efficacy: 16.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265327

CATALOG NUMBER: P3AS17R159730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265327

CATALOG NUMBER: P3AS17R159730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	106	111	108	106	104	104	102	101		100	99	98		97
2	108	103	98	95	105	101	97	94	98	95	92		95	92	90		92
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87
4	97	90	84	80	95	88	83	79	86	82	78		84	81	78		82
5	93	84	78	74	91	83	78	74	81	77	73		80	76	72		78
6	88	79	73	69	87	79	73	69	77	72	69		76	71	68		74
7	84	75	69	65	83	74	69	65	73	68	64		72	67	64		71
8	80	71	65	61	79	71	65	61	69	64	61		68	64	61		67
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64
10	74	64	59	55	73	64	59	55	63	58	55		62	58	55		62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	150076
5°	138697
10°	110731
15°	83655
20°	63682
25°	48535
30°	34765
35°	22700
40°	13912
45°	8404
50°	5595
55°	4320
60°	3728
65°	3217
70°	2885
75°	2881
80°	2147
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8404 cd/sqm

TEST NUMBER: P1265327

CATALOG NUMBER: P3AS17R159730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.8	16.0
10°-20°	103.0	29.6
20°-30°	91.7	26.3
30°-40°	54.2	15.6
40°-50°	22.3	6.4
50°-60°	10.5	3.0
60°-70°	6.4	1.8
70°-80°	3.4	1.0
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	250.5	72.0
0°-40°	304.7	87.6
0°-60°	337.4	97.0
0°-90°	348.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	348.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	684	
5°	630	56
15°	368	103
25°	201	92
35°	85	54
45°	27	22
55°	11	10
65°	6	6
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1265327

CATALOG NUMBER: P3AS17R159730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	684.4
1°	682.7
2°	677.6
3°	667.4
4°	650.4
5°	630.1
6°	608.1
7°	582.1
8°	554.9
9°	527.3
10°	497.3
12.5°	428.9
15°	368.5
17.5°	316.5
20°	272.9
22.5°	234.5
25°	200.6
27.5°	167.8
30°	137.3
32.5°	109.6
35°	84.8
37.5°	65.0
40°	48.6
42.5°	36.2
45°	27.1
47.5°	20.9
50°	16.4
52.5°	13.6
55°	11.3
57.5°	9.6
60°	8.5
62.5°	7.3
65°	6.2
67.5°	5.7
70°	4.5
72.5°	4.0
75°	3.4
77.5°	2.3
80°	1.7
82.5°	1.1
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)