

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265961

Luminaire Tested: P3AS20R609730D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265961
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609730D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 612.0 lumens
Efficiency: N/A
Efficacy: 21.2 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265961

CATALOG NUMBER: P3AS20R609730D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265961

CATALOG NUMBER: P3AS20R609730D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	108632
5°	107418
10°	103694
15°	97980
20°	90308
25°	81779
30°	72593
35°	62024
40°	49321
45°	34794
50°	20775
55°	10513
60°	10087
65°	9236
70°	8591
75°	8218
80°	7450
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 34794 cd/sqm

TEST NUMBER: P1265961

CATALOG NUMBER: P3AS20R609730D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.9	7.5
10°-20°	120.6	19.7
20°-30°	154.9	25.3
30°-40°	143.6	23.5
40°-50°	87.4	14.3
50°-60°	29.1	4.8
60°-70°	17.7	2.9
70°-80°	10.0	1.6
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	321.3	52.5
0°-40°	464.9	76.0
0°-60°	581.5	95.0
0°-90°	612.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	612.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	495	
5°	488	46
15°	432	121
25°	338	155
35°	232	144
45°	112	87
55°	28	29
65°	18	18
75°	10	10
85°	2	3
90°	0	

TEST NUMBER: P1265961

CATALOG NUMBER: P3AS20R609730D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	495.4
2.5°	493.2
5°	488.0
7.5°	478.3
10°	465.7
12.5°	450.1
15°	431.6
17.5°	410.0
20°	387.0
22.5°	362.5
25°	338.0
27.5°	312.7
30°	286.7
32.5°	260.7
35°	231.7
37.5°	201.3
40°	172.3
42.5°	141.9
45°	112.2
47.5°	86.9
50°	60.9
52.5°	36.4
55°	27.5
57.5°	25.3
60°	23.0
62.5°	20.1
65°	17.8
67.5°	15.6
70°	13.4
72.5°	11.1
75°	9.7
77.5°	7.4
80°	5.9
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

(END OF REPORT)