

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265962

Luminaire Tested: P3AS20R609730D010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265962
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R609730D010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1249.0 lumens
Efficiency: N/A
Efficacy: 43.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265962
CATALOG NUMBER: P3AS20R609730D010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1265962
 CATALOG NUMBER: P3AS20R609730D010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91	91	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82	82	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74	74	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67	67	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61	61	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56	56	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51	51	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47	47	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44	44	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41	41	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	221715
5°	219216
10°	211642
15°	199933
20°	184303
25°	166873
30°	148149
35°	126618
40°	100674
45°	70984
50°	42404
55°	21447
60°	20612
65°	18887
70°	17503
75°	16691
80°	15280
85°	11322

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 70984 cd/sqm



TEST NUMBER: P1265962
 CATALOG NUMBER: P3AS20R609730D010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.6	7.5
10°-20°	246.1	19.7
20°-30°	316.1	25.3
30°-40°	293.0	23.5
40°-50°	178.4	14.3
50°-60°	59.4	4.8
60°-70°	36.2	2.9
70°-80°	20.4	1.6
80°-90°	5.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	655.8	52.5
0°-40°	948.8	76.0
0°-60°	1186.7	95.0
0°-90°	1249.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1249.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1011	
5°	996	94
15°	881	246
25°	690	316
35°	473	293
45°	229	178
55°	56	59
65°	36	36
75°	20	20
85°	4	6
90°	0	



TEST NUMBER: P1265962
CATALOG NUMBER: P3AS20R609730D010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1011.1
2.5°	1006.6
5°	995.9
7.5°	976.2
10°	950.5
12.5°	918.6
15°	880.7
17.5°	836.8
20°	789.8
22.5°	739.8
25°	689.7
27.5°	638.2
30°	585.1
32.5°	532.1
35°	473.0
37.5°	410.8
40°	351.7
42.5°	289.5
45°	228.9
47.5°	177.4
50°	124.3
52.5°	74.3
55°	56.1
57.5°	51.5
60°	47.0
62.5°	40.9
65°	36.4
67.5°	31.8
70°	27.3
72.5°	22.7
75°	19.7
77.5°	15.2
80°	12.1
82.5°	7.6
85°	4.5
87.5°	3.0
90°	0.0

(END OF REPORT)