

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265335

Luminaire Tested: P3AS17R159730DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265335
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R159730DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 538.0 lumens
Efficiency: N/A
Efficacy: 25.4 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265335

CATALOG NUMBER: P3AS17R159730DE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1265335

CATALOG NUMBER: P3AS17R159730DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95
2	105	99	94	90	102	97	92	89	94	90	87		91	87	85		88
3	99	91	85	80	96	89	84	80	87	82	78		84	80	77		82
4	93	84	78	73	91	83	77	72	81	76	71		79	74	71		77
5	88	78	72	67	86	77	71	67	76	70	66		74	69	65		72
6	83	73	67	62	82	73	66	62	71	65	61		70	65	61		68
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	59	52	48	68	58	52	48	57	52	48		56	51	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	201365
5°	184899
10°	147314
15°	110103
20°	83611
25°	63318
30°	46843
35°	33462
40°	22900
45°	16033
50°	13646
55°	13381
60°	13902
65°	14684
70°	14938
75°	15504
80°	16795
85°	16857

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 19656 cd/sqm

TEST NUMBER: P1265335

CATALOG NUMBER: P3AS17R159730DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.4	13.8
10°-20°	136.0	25.3
20°-30°	120.5	22.4
30°-40°	78.9	14.7
40°-50°	42.2	7.8
50°-60°	31.9	5.9
60°-70°	27.4	5.1
70°-80°	18.9	3.5
80°-90°	7.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	330.9	61.5
0°-40°	409.9	76.2
0°-60°	483.9	90.0
0°-90°	538.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	538.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	918	
5°	840	74
15°	485	136
25°	262	121
35°	125	79
45°	52	42
55°	35	32
65°	28	27
75°	18	19
85°	7	8
90°	0	

TEST NUMBER: P1265335

CATALOG NUMBER: P3AS17R159730DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	918.3
2.5°	896.6
5°	840.0
7.5°	756.6
10°	661.6
12.5°	570.0
15°	485.0
17.5°	416.6
20°	358.3
22.5°	306.7
25°	261.7
27.5°	221.7
30°	185.0
32.5°	153.3
35°	125.0
37.5°	100.0
40°	80.0
42.5°	63.3
45°	51.7
47.5°	45.0
50°	40.0
52.5°	38.3
55°	35.0
57.5°	33.3
60°	31.7
62.5°	30.0
65°	28.3
67.5°	25.0
70°	23.3
72.5°	20.0
75°	18.3
77.5°	15.0
80°	13.3
82.5°	11.7
85°	6.7
87.5°	3.3
90°	0.0

(END OF REPORT)