

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265341

Luminaire Tested: P3AS17R209730DE010 E3CD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265341
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R209730DE010 E3CD1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3CD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1458.1 lumens
Efficiency: N/A
Efficacy: 68.8 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265341
CATALOG NUMBER: P3AS17R209730DE010 E3CD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1265341

CATALOG NUMBER: P3AS17R209730DE010 E3CD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	98	98	98
2	112	109	106	104	110	108	105	103	104	103	101	102	100	99	99	98	97	97	98	97	95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	95	96	95	93
4	107	102	99	96	105	101	98	96	99	97	94	97	95	93	96	94	92	96	94	92	91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	94	92	91	90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	93	90	89	88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	91	89	87	86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	89	87	85	85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	88	86	84	83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	86	84	82	86	84	82	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2264446
5°	1965458
10°	1214451
15°	421819
20°	129535
25°	45801
30°	16939
35°	6799
40°	3635
45°	1427
50°	785
55°	879
60°	1009
65°	623
70°	769
75°	1017
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1427 cd/sqm



TEST NUMBER: P1265341
 CATALOG NUMBER: P3AS17R209730DE010 E3CD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	741.1	50.8
10°-20°	588.0	40.3
20°-30°	101.8	7.0
30°-40°	18.5	1.3
40°-50°	4.2	0.3
50°-60°	2.1	0.1
60°-70°	1.3	0.1
70°-80°	1.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1430.8	98.1
0°-40°	1449.3	99.4
0°-60°	1455.6	99.8
0°-90°	1458.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1458.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10327	
5°	8929	741
15°	1858	588
25°	189	102
35°	25	18
45°	5	4
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1265341
CATALOG NUMBER: P3AS17R209730DE010 E3CD1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	10326.7
1°	10277.0
2°	10080.9
3°	9765.8
4°	9396.5
5°	8929.1
6°	8393.6
7°	7770.4
8°	7060.6
9°	6263.2
10°	5454.2
12.5°	3440.3
15°	1858.1
17.5°	992.5
20°	555.1
22.5°	317.4
25°	189.3
27.5°	115.4
30°	66.9
32.5°	39.2
35°	25.4
37.5°	17.3
40°	12.7
42.5°	8.1
45°	4.6
47.5°	2.3
50°	2.3
52.5°	2.3
55°	2.3
57.5°	2.3
60°	2.3
62.5°	1.2
65°	1.2
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	1.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)