

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265990

Luminaire Tested: P3AS20R659730D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265990
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659730D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 585.0 lumens
Efficiency: N/A
Efficacy: 20.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265990

CATALOG NUMBER: P3AS20R659730D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265990

CATALOG NUMBER: P3AS20R659730D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	104093
5°	102707
10°	99263
15°	93599
20°	86341
25°	78367
30°	69428
35°	59080
40°	47002
45°	33182
50°	19274
55°	10513
60°	9780
65°	8873
70°	8078
75°	7540
80°	6566
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 33182 cd/sqm

TEST NUMBER: P1265990

CATALOG NUMBER: P3AS20R659730D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.9	7.5
10°-20°	115.4	19.7
20°-30°	148.3	25.3
30°-40°	137.2	23.4
40°-50°	82.8	14.2
50°-60°	28.3	4.8
60°-70°	17.0	2.9
70°-80°	9.6	1.6
80°-90°	2.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	307.5	52.6
0°-40°	444.7	76.0
0°-60°	555.7	95.0
0°-90°	585.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	585.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	475	
5°	467	44
15°	412	115
25°	324	148
35°	221	137
45°	107	83
55°	28	28
65°	17	17
75°	9	10
85°	2	3
90°	0	

TEST NUMBER: P1265990

CATALOG NUMBER: P3AS20R659730D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	474.7
2.5°	472.5
5°	466.6
7.5°	457.7
10°	445.8
12.5°	430.9
15°	412.3
17.5°	392.3
20°	370.0
22.5°	347.0
25°	323.9
27.5°	299.4
30°	274.2
32.5°	248.9
35°	220.7
37.5°	193.2
40°	164.2
42.5°	135.2
45°	107.0
47.5°	81.0
50°	56.5
52.5°	35.7
55°	27.5
57.5°	24.5
60°	22.3
62.5°	19.3
65°	17.1
67.5°	14.9
70°	12.6
72.5°	11.1
75°	8.9
77.5°	7.4
80°	5.2
82.5°	3.7
85°	2.2
87.5°	1.5
90°	0.0

(END OF REPORT)