

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266021

Luminaire Tested: P3AS20R709730D010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266021
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709730D010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R70 optic, 3000K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1089.0 lumens
Efficiency: N/A
Efficacy: 37.8 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266021

CATALOG NUMBER: P3AS20R709730D010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1266021

CATALOG NUMBER: P3AS20R709730D010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	255440
5°	250737
10°	236446
15°	214576
20°	187710
25°	158332
30°	129640
35°	100572
40°	71992
45°	45555
50°	22754
55°	13916
60°	11973
65°	11000
70°	9681
75°	8981
80°	7703
85°	7548

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 45555 cd/sqm

TEST NUMBER: P1266021

CATALOG NUMBER: P3AS20R709730D010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	106.3	9.8
10°-20°	263.0	24.2
20°-30°	299.5	27.5
30°-40°	234.2	21.5
40°-50°	115.1	10.6
50°-60°	35.4	3.3
60°-70°	21.0	1.9
70°-80°	11.2	1.0
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	668.9	61.4
0°-40°	903.1	82.9
0°-60°	1053.6	96.7
0°-90°	1089.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1089.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1165	
5°	1139	106
15°	945	263
25°	654	300
35°	376	234
45°	147	115
55°	36	35
65°	21	21
75°	11	11
85°	3	3
90°	0	

TEST NUMBER: P1266021

CATALOG NUMBER: P3AS20R709730D010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1164.9
2.5°	1158.8
5°	1139.1
7.5°	1107.3
10°	1061.9
12.5°	1008.9
15°	945.2
17.5°	877.1
20°	804.4
22.5°	728.6
25°	654.4
27.5°	581.7
30°	512.0
32.5°	442.3
35°	375.7
37.5°	312.0
40°	251.5
42.5°	195.4
45°	146.9
47.5°	103.0
50°	66.7
52.5°	43.9
55°	36.4
57.5°	31.8
60°	27.3
62.5°	24.2
65°	21.2
67.5°	18.2
70°	15.1
72.5°	12.1
75°	10.6
77.5°	9.1
80°	6.1
82.5°	4.5
85°	3.0
87.5°	1.5
90°	0.0

(END OF REPORT)