

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266104

Luminaire Tested: P3AS02R109735DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266104
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R109735DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R10 optic, 3500K CCT AND, 97CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 116.0 lumens
Efficiency: N/A
Efficacy: 30.5 lumens/watt
Spacing Criteria (0/90/45): 0.51 / 0.51 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266104

CATALOG NUMBER: P3AS02R109735DE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1266104

CATALOG NUMBER: P3AS02R109735DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95
2	105	99	94	90	102	97	92	89	94	90	87		91	87	85		88
3	99	91	85	80	96	89	84	80	87	82	78		84	80	77		82
4	93	84	78	73	91	83	77	72	81	76	72		79	74	71		77
5	88	78	72	67	86	77	71	67	76	70	66		74	69	65		72
6	83	73	67	62	82	73	66	62	71	65	61		70	65	61		68
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	59	52	48	68	58	52	48	57	52	48		56	51	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	43418
5°	39863
10°	31774
15°	23746
20°	18038
25°	13646
30°	10103
35°	7228
40°	4924
45°	3442
50°	2934
55°	2867
60°	2982
65°	3165
70°	3206
75°	3389
80°	3662
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 4200 cd/sqm

TEST NUMBER: P1266104

CATALOG NUMBER: P3AS02R109735DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.0	13.8
10°-20°	29.3	25.3
20°-30°	26.0	22.4
30°-40°	17.0	14.7
40°-50°	9.1	7.8
50°-60°	6.9	5.9
60°-70°	5.9	5.1
70°-80°	4.1	3.5
80°-90°	1.6	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	71.4	61.5
0°-40°	88.4	76.2
0°-60°	104.3	90.0
0°-90°	116.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	116.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	198	
5°	181	16
15°	105	29
25°	56	26
35°	27	17
45°	11	9
55°	8	7
65°	6	6
75°	4	4
85°	1	2
90°	0	

TEST NUMBER: P1266104

CATALOG NUMBER: P3AS02R109735DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	198.0
2.5°	193.3
5°	181.1
7.5°	163.1
10°	142.7
12.5°	122.9
15°	104.6
17.5°	89.8
20°	77.3
22.5°	66.1
25°	56.4
27.5°	47.8
30°	39.9
32.5°	33.1
35°	27.0
37.5°	21.6
40°	17.2
42.5°	13.7
45°	11.1
47.5°	9.7
50°	8.6
52.5°	8.3
55°	7.5
57.5°	7.2
60°	6.8
62.5°	6.5
65°	6.1
67.5°	5.4
70°	5.0
72.5°	4.3
75°	4.0
77.5°	3.2
80°	2.9
82.5°	2.5
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)