

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266186

Luminaire Tested: P3AS02R209735DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266186
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R209735DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 88.0 lumens
Efficiency: N/A
Efficacy: 24.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266186

CATALOG NUMBER: P3AS02R209735DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1266186

CATALOG NUMBER: P3AS02R209735DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	109	106	104	110	107	105	102	103	101	99	99	98	96	96	95	93	91		
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	90	87	85	83		
3	100	93	87	82	98	91	86	82	88	84	80	86	82	79	84	81	78	76		
4	94	86	79	75	92	85	79	74	82	77	73	80	76	72	78	75	72	70		
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65		
6	84	74	68	63	82	73	67	63	72	66	62	70	65	62	69	65	61	60		
7	80	69	63	58	78	69	62	58	67	62	58	66	61	57	65	60	57	55		
8	75	65	59	54	74	64	58	54	63	58	54	62	57	53	61	57	53	52		
9	72	61	55	50	70	61	55	50	60	54	50	59	54	50	58	53	50	48		
10	68	58	51	47	67	57	51	47	56	51	47	56	50	47	55	50	47	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21775
5°	21175
10°	19483
15°	17162
20°	14701
25°	12364
30°	10002
35°	7602
40°	5410
45°	3566
50°	2217
55°	1453
60°	1316
65°	1193
70°	1154
75°	1017
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3566 cd/sqm

TEST NUMBER: P1266186

CATALOG NUMBER: P3AS02R209735DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.9	10.1
10°-20°	21.0	23.9
20°-30°	23.4	26.5
30°-40°	17.8	20.3
40°-50°	9.1	10.4
50°-60°	3.8	4.3
60°-70°	2.3	2.6
70°-80°	1.3	1.5
80°-90°	0.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	53.3	60.5
0°-40°	71.1	80.8
0°-60°	84.0	95.4
0°-90°	88.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	88.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	99	
5°	96	9
15°	76	21
25°	51	23
35°	28	18
45°	12	9
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1266186

CATALOG NUMBER: P3AS02R209735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	99.3
1°	99.4
2°	98.9
3°	98.4
4°	97.5
5°	96.2
6°	94.8
7°	93.2
8°	91.6
9°	89.5
10°	87.5
12.5°	81.7
15°	75.6
17.5°	69.3
20°	63.0
22.5°	56.8
25°	51.1
27.5°	45.4
30°	39.5
32.5°	33.9
35°	28.4
37.5°	23.6
40°	18.9
42.5°	14.9
45°	11.5
47.5°	8.7
50°	6.5
52.5°	4.8
55°	3.8
57.5°	3.5
60°	3.0
62.5°	2.7
65°	2.3
67.5°	2.0
70°	1.8
72.5°	1.5
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.3
87.5°	0.1
90°	0.0

(END OF REPORT)