

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265432

Luminaire Tested: P3AS17R359730DE010 E3D1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265432
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R359730DE010 E3D1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3000K CCT AND, 97CRI , E3D1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1466.0 lumens
Efficiency: N/A
Efficacy: 69.2 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265432

CATALOG NUMBER: P3AS17R359730DE010 E3D1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1265432

CATALOG NUMBER: P3AS17R359730DE010 E3D1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	113	111	109		112	110	109	107		106	105	104		103	102	101		99	99	98
2	111	107	104	101		109	105	103	100		102	100	98		99	98	96		97	95	94
3	107	102	98	95		105	101	97	95		98	96	93		96	94	92		94	92	90
4	104	98	94	91		102	97	93	90		95	92	89		93	90	88		91	89	87
5	100	94	90	87		99	93	89	86		92	88	86		90	87	85		89	86	84
6	97	91	86	83		96	90	86	83		89	85	82		87	84	82		86	83	81
7	94	87	83	80		93	87	83	80		86	82	79		85	81	79		84	81	79
8	91	84	80	77		90	84	80	77		83	79	77		82	79	76		81	78	76
9	89	82	77	74		88	81	77	74		80	77	74		80	76	74		79	76	74
10	86	79	75	72		85	79	75	72		78	74	72		77	74	72		77	74	71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	955932
5°	936449
10°	871193
15°	638710
20°	327068
25°	117878
30°	45906
35°	16062
40°	6612
45°	1799
50°	1569
55°	1759
60°	1535
65°	1193
70°	1475
75°	1949
80°	1515
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 2016 cd/sqm

TEST NUMBER: P1265432

CATALOG NUMBER: P3AS17R359730DE010 E3D1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	396.6	27.1
10°-20°	744.1	50.8
20°-30°	263.5	18.0
30°-40°	46.1	3.1
40°-50°	6.7	0.5
50°-60°	3.7	0.3
60°-70°	2.7	0.2
70°-80°	2.0	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1404.2	95.8
0°-40°	1450.4	98.9
0°-60°	1460.8	99.6
0°-90°	1466.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1466.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4359	
5°	4254	397
15°	2814	744
25°	487	263
35°	60	46
45°	6	7
55°	5	4
65°	2	3
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1265432

CATALOG NUMBER: P3AS17R359730DE010 E3D1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	4359.4
1°	4358.2
2°	4344.4
3°	4317.8
4°	4293.6
5°	4254.3
6°	4213.9
7°	4168.9
8°	4113.5
9°	4026.9
10°	3912.6
11°	3754.4
12°	3563.9
13°	3337.7
14°	3088.3
15°	2813.5
17.5°	2095.4
20°	1401.6
22.5°	845.1
25°	487.2
27.5°	290.9
30°	181.3
32.5°	105.1
35°	60.0
37.5°	38.1
40°	23.1
42.5°	11.5
45°	5.8
47.5°	4.6
50°	4.6
52.5°	4.6
55°	4.6
57.5°	3.5
60°	3.5
62.5°	3.5
65°	2.3
67.5°	2.3
70°	2.3
72.5°	2.3
75°	2.3
77.5°	1.2
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0



TEST NUMBER: P1265432

CATALOG NUMBER: P3AS17R359730DE010 E3D1MW

CANDELA DISTRIBUTION (continued):



(END OF REPORT)