

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266221

Luminaire Tested: P3AS02R259735DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266221
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259735DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 146.0 lumens
Efficiency: N/A
Efficacy: 40.6 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266221

CATALOG NUMBER: P3AS02R259735DE010 E3DLP1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1266221

CATALOG NUMBER: P3AS02R259735DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	108	105	111	108	106	104	104	102	101		100	99	98		97
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92
3	102	95	90	86	100	94	89	86	91	87	84		89	86	83		87
4	97	89	84	79	95	88	83	79	86	81	78		84	80	77		82
5	92	84	78	74	91	83	77	73	81	76	73		79	75	72		78
6	88	79	73	69	86	78	72	68	77	72	68		75	71	67		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	65	60	79	70	64	60	69	64	60		68	63	60		67
9	76	67	61	57	75	66	61	57	65	60	57		64	60	57		64
10	73	64	58	54	72	63	58	54	62	57	54		62	57	54		61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	53000
5°	50847
10°	44555
15°	35800
20°	27512
25°	20808
30°	15040
35°	9985
40°	6069
45°	3535
50°	2252
55°	1835
60°	1579
65°	1401
70°	1154
75°	1186
80°	884
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3535 cd/sqm

TEST NUMBER: P1266221

CATALOG NUMBER: P3AS02R259735DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.0	14.4
10°-20°	43.6	29.9
20°-30°	39.4	27.0
30°-40°	23.7	16.2
40°-50°	9.4	6.4
50°-60°	4.3	3.0
60°-70°	2.6	1.8
70°-80°	1.4	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	104.1	71.3
0°-40°	127.8	87.5
0°-60°	141.6	96.9
0°-90°	146.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	146.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	242	
5°	231	21
15°	158	44
25°	86	39
35°	37	24
45°	11	9
55°	5	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1266221

CATALOG NUMBER: P3AS02R259735DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	241.7
1°	241.7
2°	240.6
3°	238.1
4°	234.9
5°	231.0
6°	226.0
7°	220.3
8°	213.7
9°	207.1
10°	200.1
11°	191.9
12°	183.5
13°	175.0
14°	166.6
15°	157.7
17.5°	136.8
20°	117.9
22.5°	100.8
25°	86.0
27.5°	72.2
30°	59.4
32.5°	47.8
35°	37.3
37.5°	28.5
40°	21.2
42.5°	15.5
45°	11.4
47.5°	8.6
50°	6.6
52.5°	5.5
55°	4.8
57.5°	4.1
60°	3.6
62.5°	3.0
65°	2.7
67.5°	2.3
70°	1.8
72.5°	1.6
75°	1.4
77.5°	1.1
80°	0.7
82.5°	0.5
85°	0.5
87.5°	0.2



TEST NUMBER: P1266221

CATALOG NUMBER: P3AS02R259735DE010 E3DLP1LI

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)