

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266226

Luminaire Tested: P3AS02R259735DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266226
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259735DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 182.0 lumens
Efficiency: N/A
Efficacy: 50.6 lumens/watt
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.71
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266226

CATALOG NUMBER: P3AS02R259735DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1266226

CATALOG NUMBER: P3AS02R259735DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87
3	97	89	83	78	95	88	82	77	85	80	76		83	78	75		80
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74
5	86	76	68	63	84	75	68	63	73	67	62		71	66	62		69
6	81	70	63	58	79	69	62	57	68	62	57		66	61	57		65
7	76	65	58	53	75	64	58	53	63	57	53		62	56	52		61
8	72	61	54	49	71	60	54	49	59	53	49		58	53	49		57
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	43		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	47496
5°	45080
10°	39033
15°	31782
20°	25109
25°	20033
30°	16230
35°	13224
40°	10963
45°	9241
50°	7812
55°	6881
60°	6008
65°	5241
70°	4616
75°	3897
80°	2904
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9241 cd/sqm

TEST NUMBER: P1266226

CATALOG NUMBER: P3AS02R259735DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.6	10.2
10°-20°	38.8	21.3
20°-30°	38.3	21.0
30°-40°	31.2	17.1
40°-50°	23.1	12.7
50°-60°	16.1	8.9
60°-70°	10.1	5.5
70°-80°	4.9	2.7
80°-90°	0.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	95.7	52.6
0°-40°	126.8	69.7
0°-60°	166.1	91.3
0°-90°	182.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	182.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	217	
5°	205	19
15°	140	39
25°	83	38
35°	49	31
45°	30	23
55°	18	16
65°	10	10
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1266226

CATALOG NUMBER: P3AS02R259735DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	216.6
2.5°	213.6
5°	204.8
7.5°	191.4
10°	175.3
12.5°	157.7
15°	140.0
17.5°	122.7
20°	107.6
22.5°	94.5
25°	82.8
27.5°	72.6
30°	64.1
32.5°	56.3
35°	49.4
37.5°	43.5
40°	38.3
42.5°	33.7
45°	29.8
47.5°	26.2
50°	22.9
52.5°	20.3
55°	18.0
57.5°	15.7
60°	13.7
62.5°	11.8
65°	10.1
67.5°	8.5
70°	7.2
72.5°	5.9
75°	4.6
77.5°	3.3
80°	2.3
82.5°	1.3
85°	0.7
87.5°	0.3
90°	0.0

(END OF REPORT)