

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266227

Luminaire Tested: P3AS02R259735DE010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266227
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R259735DE010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 97CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 131.0 lumens
Efficiency: N/A
Efficacy: 36.4 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.65
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266227

CATALOG NUMBER: P3AS02R259735DE010 E3PHLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1266227

CATALOG NUMBER: P3AS02R259735DE010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	97	90	84	80	87	82	78		84	80	77		82
4	93	84	78	73	91	83	77	73	81	76	72		79	74	71		77
5	88	79	72	67	86	78	71	67	76	70	66		74	69	66		72
6	84	74	67	62	82	73	66	62	71	66	61		70	65	61		68
7	79	69	63	58	78	68	62	58	67	61	57		66	61	57		65
8	76	65	59	54	74	65	58	54	63	58	54		62	57	54		61
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	59	52	48	68	58	52	48	57	52	48		56	51	48		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44010
5°	41580
10°	35337
15°	27991
20°	21282
25°	15872
30°	11546
35°	8165
40°	5553
45°	3876
50°	3241
55°	3135
60°	3289
65°	3424
70°	3334
75°	3643
80°	4167
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 4368 cd/sqm

TEST NUMBER: P1266227

CATALOG NUMBER: P3AS02R259735DE010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.0	13.0
10°-20°	34.1	26.1
20°-30°	30.2	23.1
30°-40°	19.3	14.7
40°-50°	10.2	7.8
50°-60°	7.5	5.7
60°-70°	6.4	4.9
70°-80°	4.5	3.4
80°-90°	1.8	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	81.4	62.1
0°-40°	100.7	76.8
0°-60°	118.4	90.3
0°-90°	131.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	131.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	201	
5°	189	17
15°	123	34
25°	66	30
35°	30	19
45°	12	10
55°	8	7
65°	7	6
75°	4	5
85°	2	2
90°	0	

TEST NUMBER: P1266227

CATALOG NUMBER: P3AS02R259735DE010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	200.7
2.5°	197.8
5°	188.9
7.5°	175.1
10°	158.7
12.5°	141.0
15°	123.3
17.5°	106.3
20°	91.2
22.5°	77.4
25°	65.6
27.5°	55.1
30°	45.6
32.5°	37.4
35°	30.5
37.5°	24.3
40°	19.4
42.5°	15.4
45°	12.5
47.5°	10.8
50°	9.5
52.5°	8.9
55°	8.2
57.5°	7.9
60°	7.5
62.5°	6.9
65°	6.6
67.5°	5.9
70°	5.2
72.5°	4.9
75°	4.3
77.5°	3.6
80°	3.3
82.5°	2.6
85°	1.6
87.5°	0.7
90°	0.0

(END OF REPORT)