

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265480

Luminaire Tested: P3AS17R409730DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265480
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R409730DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 3000K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 848.0 lumens
Efficiency: N/A
Efficacy: 40.0 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265480
CATALOG NUMBER: P3AS17R409730DE010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1265480
 CATALOG NUMBER: P3AS17R409730DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86				86
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80				80
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74				74
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69				69
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65				65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	62	61				61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58				58
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54				54
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	264058
5°	258705
10°	240877
15°	209944
20°	169181
25°	126806
30°	89153
35°	58410
40°	35352
45°	21118
50°	12588
55°	10169
60°	9122
65°	7783
70°	7373
75°	5846
80°	5809
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 21118 cd/sqm



TEST NUMBER: P1265480
 CATALOG NUMBER: P3AS17R409730DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.1	12.9
10°-20°	254.7	30.0
20°-30°	240.0	28.3
30°-40°	138.8	16.4
40°-50°	55.3	6.5
50°-60°	24.5	2.9
60°-70°	15.1	1.8
70°-80°	7.9	0.9
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	603.9	71.2
0°-40°	742.6	87.6
0°-60°	822.4	97.0
0°-90°	848.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	848.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1204	
5°	1175	109
15°	925	255
25°	524	240
35°	218	139
45°	68	55
55°	27	24
65°	15	15
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1265480
CATALOG NUMBER: P3AS17R409730DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1204.2
2.5°	1197.2
5°	1175.3
7.5°	1134.9
10°	1081.8
12.5°	1010.2
15°	924.8
17.5°	828.9
20°	725.0
22.5°	621.1
25°	524.1
27.5°	434.1
30°	352.1
32.5°	280.5
35°	218.2
37.5°	165.1
40°	123.5
42.5°	92.4
45°	68.1
47.5°	49.6
50°	36.9
52.5°	30.0
55°	26.6
57.5°	24.2
60°	20.8
62.5°	17.3
65°	15.0
67.5°	12.7
70°	11.5
72.5°	9.2
75°	6.9
77.5°	5.8
80°	4.6
82.5°	3.5
85°	2.3
87.5°	1.2
90°	0.0

(END OF REPORT)