

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266268

Luminaire Tested: P3AS02R359735DE010 E3DL1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266268
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359735DE010 E3DL1H
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DL1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 239.0 lumens
Efficiency: N/A
Efficacy: 66.4 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266268

CATALOG NUMBER: P3AS02R359735DE010 E3DL1H

Luminous Intensity Polar Plot



TEST NUMBER: P1266268

CATALOG NUMBER: P3AS02R359735DE010 E3DL1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	114	112	109	107		112	109	107	106		105	104	102		102	100	99		98	97	96
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	93	91
3	105	99	95	91		103	98	94	90		95	92	89		93	90	88		91	88	86
4	100	94	89	85		99	93	88	85		91	87	84		89	85	83		87	84	82
5	96	89	84	80		95	88	83	80		86	82	79		85	81	78		83	80	78
6	92	85	80	76		91	84	79	76		83	78	75		81	77	75		80	77	74
7	89	81	76	72		88	80	75	72		79	75	71		78	74	71		77	73	71
8	85	77	72	69		84	77	72	68		76	71	68		75	71	68		74	70	68
9	82	74	69	66		81	74	69	65		73	68	65		72	68	65		71	67	65
10	79	71	66	63		78	71	66	63		70	66	63		69	65	62		69	65	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	120539
5°	115848
10°	100933
15°	77322
20°	51734
25°	31308
30°	17952
35°	10038
40°	5324
45°	2760
50°	1330
55°	1032
60°	1009
65°	830
70°	898
75°	763
80°	884
85°	503

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2760 cd/sqm

TEST NUMBER: P1266268

CATALOG NUMBER: P3AS02R359735DE010 E3DL1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.9	20.0
10°-20°	92.8	38.8
20°-30°	60.8	25.4
30°-40°	24.6	10.3
40°-50°	7.4	3.1
50°-60°	2.5	1.1
60°-70°	1.7	0.7
70°-80°	1.0	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	201.4	84.3
0°-40°	226.1	94.6
0°-60°	236.0	98.7
0°-90°	239.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	239.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	550	
5°	526	48
15°	341	93
25°	129	61
35°	38	25
45°	9	7
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1266268

CATALOG NUMBER: P3AS02R359735DE010 E3DL1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	549.7
1°	548.8
2°	546.3
3°	541.3
4°	535.4
5°	526.3
6°	514.9
7°	502.2
8°	487.9
9°	471.5
10°	453.3
11°	433.1
12°	411.9
13°	388.3
14°	365.8
15°	340.6
17.5°	279.4
20°	221.7
22.5°	170.5
25°	129.4
27.5°	96.4
30°	70.9
32.5°	52.1
35°	37.5
37.5°	26.6
40°	18.6
42.5°	13.0
45°	8.9
47.5°	5.9
50°	3.9
52.5°	3.0
55°	2.7
57.5°	2.5
60°	2.3
62.5°	2.0
65°	1.6
67.5°	1.4
70°	1.4
72.5°	1.1
75°	0.9
77.5°	0.7
80°	0.7
82.5°	0.5
85°	0.2
87.5°	0.2



TEST NUMBER: P1266268
CATALOG NUMBER: P3AS02R359735DE010 E3DL1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)