

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265515

Luminaire Tested: P3AS17R509730DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509730DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1603.0 lumens
Efficiency: N/A
Efficacy: 75.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265515

CATALOG NUMBER: P3AS17R509730DE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1265515

CATALOG NUMBER: P3AS17R509730DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	97	97	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	82	82	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	77	77	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	73	73	72
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	70	70	68
8	84	76	71	67	83	76	71	67	75	70	67	74	69	66	73	69	66	66	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	63	63	62
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	60	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	560174
5°	545277
10°	520342
15°	471058
20°	407552
25°	334302
30°	192030
35°	59642
40°	16030
45°	5613
50°	1365
55°	421
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5613 cd/sqm

TEST NUMBER: P1265515

CATALOG NUMBER: P3AS17R509730DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	232.0	14.5
10°-20°	575.0	35.9
20°-30°	604.3	37.7
30°-40°	173.0	10.8
40°-50°	16.9	1.1
50°-60°	1.4	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1411.3	88.0
0°-40°	1584.3	98.8
0°-60°	1602.5	100.0
0°-90°	1603.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1603.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2555	
5°	2477	232
15°	2075	575
25°	1382	604
35°	223	173
45°	18	17
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1265515

CATALOG NUMBER: P3AS17R509730DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	2554.6
1°	2550.7
2°	2539.4
3°	2523.0
4°	2500.9
5°	2477.2
6°	2451.7
7°	2424.6
8°	2399.1
9°	2369.7
10°	2336.9
11°	2299.0
12°	2255.5
13°	2201.2
14°	2142.4
15°	2075.0
16°	2003.8
17°	1934.8
18°	1864.1
19°	1801.9
20°	1746.5
21°	1693.3
22°	1632.8
23°	1563.2
24°	1481.8
25°	1381.7
26°	1273.1
27°	1152.1
28°	1031.6
29°	901.5
30°	758.4
31°	624.4
32°	501.1
32.5°	447.4
33°	393.1
34°	301.4
35°	222.8
36°	163.4
37°	121.6
37.5°	105.2
38°	91.1
39°	70.7
40°	56.0
42.5°	31.7
45°	18.1



TEST NUMBER: P1265515

CATALOG NUMBER: P3AS17R509730DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
47.5°	10.2
50°	4.0
52.5°	1.7
55°	1.1
57.5°	1.1
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.6
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)