

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266273

Luminaire Tested: P3AS02R359735DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266273
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R359735DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 90.0 lumens
Efficiency: N/A
Efficacy: 25.0 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266273
CATALOG NUMBER: P3AS02R359735DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1266273

CATALOG NUMBER: P3AS02R359735DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20569
5°	20119
10°	18837
15°	16913
20°	14725
25°	12533
30°	10508
35°	8379
40°	6040
45°	3814
50°	2081
55°	1453
60°	1360
65°	1245
70°	1218
75°	1017
80°	1010
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3814 cd/sqm



TEST NUMBER: P1266273
 CATALOG NUMBER: P3AS02R359735DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	8.5	9.5
10°-20°	20.7	23.0
20°-30°	23.8	26.4
30°-40°	19.4	21.6
40°-50°	9.8	10.9
50°-60°	3.6	4.0
60°-70°	2.4	2.7
70°-80°	1.4	1.5
80°-90°	0.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	53.0	58.9
0°-40°	72.4	80.5
0°-60°	85.8	95.3
0°-90°	90.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	90.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	94	
5°	91	9
15°	74	21
25°	52	24
35°	31	19
45°	12	10
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1266273
CATALOG NUMBER: P3AS02R359735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	93.8
1°	93.6
2°	93.4
3°	93.0
4°	92.3
5°	91.4
6°	90.3
7°	89.2
8°	87.7
9°	86.3
10°	84.6
11°	82.9
12°	81.0
13°	78.9
14°	76.6
15°	74.5
17.5°	68.8
20°	63.1
22.5°	57.2
25°	51.8
27.5°	46.6
30°	41.5
32.5°	36.4
35°	31.3
37.5°	26.1
40°	21.1
42.5°	16.5
45°	12.3
47.5°	8.9
50°	6.1
52.5°	4.4
55°	3.8
57.5°	3.4
60°	3.1
62.5°	2.8
65°	2.4
67.5°	2.1
70°	1.9
72.5°	1.6
75°	1.2
77.5°	1.0
80°	0.8
82.5°	0.6
85°	0.3
87.5°	0.2



TEST NUMBER: P1266273
CATALOG NUMBER: P3AS02R359735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)