

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265524

Luminaire Tested: P3AS17R509730DE010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1265524  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R509730DE010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 97CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1299.0 lumens  
Efficiency: N/A  
Efficacy: 61.3 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 21.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1265524

CATALOG NUMBER: P3AS17R509730DE010 E3DL1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1265524

CATALOG NUMBER: P3AS17R509730DE010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 30  |     |     |  |     | 10  |     |  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 111 | 108 | 106 |  | 111 | 109 | 106 | 104 |  | 105 | 103 | 101 |  | 101 | 99  | 98  |  | 97  | 96  | 95  |
| 2   | 108 | 103 | 99  | 96  |  | 106 | 102 | 98  | 95  |  | 98  | 95  | 93  |  | 95  | 93  | 91  |  | 93  | 91  | 89  |
| 3   | 103 | 97  | 92  | 88  |  | 101 | 95  | 91  | 87  |  | 93  | 89  | 86  |  | 90  | 87  | 84  |  | 88  | 85  | 83  |
| 4   | 98  | 91  | 85  | 81  |  | 96  | 90  | 85  | 81  |  | 87  | 83  | 80  |  | 85  | 82  | 79  |  | 84  | 80  | 78  |
| 5   | 93  | 85  | 80  | 75  |  | 92  | 84  | 79  | 75  |  | 83  | 78  | 74  |  | 81  | 77  | 74  |  | 79  | 76  | 73  |
| 6   | 89  | 80  | 75  | 71  |  | 88  | 80  | 74  | 70  |  | 78  | 73  | 70  |  | 77  | 73  | 69  |  | 75  | 72  | 69  |
| 7   | 85  | 76  | 70  | 66  |  | 84  | 75  | 70  | 66  |  | 74  | 69  | 66  |  | 73  | 69  | 65  |  | 72  | 68  | 65  |
| 8   | 81  | 72  | 66  | 62  |  | 80  | 71  | 66  | 62  |  | 70  | 65  | 62  |  | 69  | 65  | 62  |  | 68  | 64  | 61  |
| 9   | 78  | 68  | 63  | 59  |  | 76  | 68  | 62  | 59  |  | 67  | 62  | 59  |  | 66  | 62  | 58  |  | 65  | 61  | 58  |
| 10  | 74  | 65  | 59  | 56  |  | 73  | 65  | 59  | 56  |  | 64  | 59  | 55  |  | 63  | 58  | 55  |  | 62  | 58  | 55  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 413585 |
| 5°  | 405238 |
| 10° | 379574 |
| 15° | 339798 |
| 20° | 285952 |
| 25° | 218238 |
| 30° | 141845 |
| 35° | 84109  |
| 40° | 48605  |
| 45° | 24344  |
| 50° | 9074   |
| 55° | 7073   |
| 60° | 6578   |
| 65° | 5967   |
| 70° | 5898   |
| 75° | 5846   |
| 80° | 5809   |
| 85° | 5787   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24344 cd/sqm

TEST NUMBER: P1265524

CATALOG NUMBER: P3AS17R509730DE010 E3DL1WMH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 171.3  | 13.2      |
| 10°-20°   | 413.9  | 31.9      |
| 20°-30°   | 406.1  | 31.3      |
| 30°-40°   | 204.6  | 15.8      |
| 40°-50°   | 64.6   | 5.0       |
| 50°-60°   | 16.8   | 1.3       |
| 60°-70°   | 11.8   | 0.9       |
| 70°-80°   | 7.3    | 0.6       |
| 80°-90°   | 2.5    | 0.2       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 991.3  | 76.3      |
| 0°-40°    | 1195.9 | 92.1      |
| 0°-60°    | 1277.3 | 98.3      |
| 0°-90°    | 1299.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1299.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1886 |      |
| 5°  | 1841 | 171  |
| 15° | 1497 | 414  |
| 25° | 902  | 406  |
| 35° | 314  | 205  |
| 45° | 78   | 65   |
| 55° | 18   | 17   |
| 65° | 12   | 12   |
| 75° | 7    | 7    |
| 85° | 2    | 3    |
| 90° | 0    |      |

TEST NUMBER: P1265524

CATALOG NUMBER: P3AS17R509730DE010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1886.1 |
| 2.5°  | 1874.5 |
| 5°    | 1841.0 |
| 7.5°  | 1781.0 |
| 10°   | 1704.7 |
| 12.5° | 1606.6 |
| 15°   | 1496.8 |
| 17.5° | 1369.8 |
| 20°   | 1225.4 |
| 22.5° | 1069.5 |
| 25°   | 902.0  |
| 27.5° | 724.2  |
| 30°   | 560.2  |
| 32.5° | 421.6  |
| 35°   | 314.2  |
| 37.5° | 232.1  |
| 40°   | 169.8  |
| 42.5° | 120.1  |
| 45°   | 78.5   |
| 47.5° | 45.0   |
| 50°   | 26.6   |
| 52.5° | 19.6   |
| 55°   | 18.5   |
| 57.5° | 16.2   |
| 60°   | 15.0   |
| 62.5° | 13.9   |
| 65°   | 11.5   |
| 67.5° | 10.4   |
| 70°   | 9.2    |
| 72.5° | 8.1    |
| 75°   | 6.9    |
| 77.5° | 5.8    |
| 80°   | 4.6    |
| 82.5° | 3.5    |
| 85°   | 2.3    |
| 87.5° | 1.2    |
| 90°   | 0.0    |

(END OF REPORT)