

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266352

Luminaire Tested: P3AS02R509735DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266352
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R509735DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 97CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 315.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266352

CATALOG NUMBER: P3AS02R509735DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1266352

CATALOG NUMBER: P3AS02R509735DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	109	107	112	110	108	106	105	104	102		102	101	99		98
2	109	105	101	98	107	103	100	97	100	97	95		97	95	93		94
3	105	99	95	91	103	98	94	90	95	92	89		93	90	88		91
4	100	94	89	85	99	92	88	85	90	87	84		88	85	83		87
5	96	89	84	80	94	88	83	79	86	82	79		84	81	78		83
6	92	84	79	75	91	83	78	75	82	78	74		81	77	74		79
7	88	80	75	71	87	79	74	71	78	74	70		77	73	70		76
8	84	76	71	67	83	76	71	67	75	70	67		74	69	66		73
9	81	73	67	64	80	72	67	64	71	67	63		70	66	63		70
10	78	69	64	61	77	69	64	61	68	64	60		67	63	60		67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	110079
5°	107154
10°	102247
15°	92577
20°	80087
25°	65689
30°	37727
35°	11725
40°	3149
45°	1116
50°	273
55°	76
60°	44
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1116 cd/sqm

TEST NUMBER: P1266352

CATALOG NUMBER: P3AS02R509735DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.6	14.5
10°-20°	113.0	35.9
20°-30°	118.8	37.7
30°-40°	34.0	10.8
40°-50°	3.3	1.1
50°-60°	0.3	0.1
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	277.3	88.0
0°-40°	311.3	98.8
0°-60°	314.9	100.0
0°-90°	315.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	315.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	502	
5°	487	46
15°	408	113
25°	272	119
35°	44	34
45°	4	3
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1266352

CATALOG NUMBER: P3AS02R509735DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	502.0
1°	501.2
2°	499.0
3°	495.8
4°	491.4
5°	486.8
6°	481.8
7°	476.4
8°	471.4
9°	465.7
10°	459.2
11°	451.8
12°	443.2
13°	432.5
14°	421.0
15°	407.8
16°	393.8
17°	380.2
18°	366.3
19°	354.1
20°	343.2
21°	332.7
22°	320.9
23°	307.2
24°	291.2
25°	271.5
26°	250.2
27°	226.4
28°	202.7
29°	177.2
30°	149.0
31°	122.7
32°	98.5
32.5°	87.9
33°	77.2
34°	59.2
35°	43.8
36°	32.1
37°	23.9
37.5°	20.7
38°	17.9
39°	13.9
40°	11.0
42.5°	6.2
45°	3.6

TEST NUMBER: P1266352

CATALOG NUMBER: P3AS02R509735DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	2.0
50°	0.8
52.5°	0.3
55°	0.2
57.5°	0.2
60°	0.1
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)