

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265579

Luminaire Tested: P3AS17R609730DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265579
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609730DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1214.0 lumens
Efficiency: N/A
Efficacy: 57.3 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265579

CATALOG NUMBER: P3AS17R609730DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1265579

CATALOG NUMBER: P3AS17R609730DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		86	83	80	79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81	77	75	73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		76	72	69	68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72	68	64	63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		67	63	60	59
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		64	59	56	55
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60	56	53	51
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		57	53	49	48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	286666
5°	283953
10°	275680
15°	258276
20°	228593
25°	191237
30°	149871
35°	108737
40°	72336
45°	45090
50°	24392
55°	7073
60°	6578
65°	5967
70°	5898
75°	5846
80°	5809
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 45090 cd/sqm

TEST NUMBER: P1265579

CATALOG NUMBER: P3AS17R609730DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.5	10.0
10°-20°	315.7	26.0
20°-30°	359.8	29.6
30°-40°	255.1	21.0
40°-50°	115.8	9.5
50°-60°	24.6	2.0
60°-70°	11.8	1.0
70°-80°	7.3	0.6
80°-90°	2.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	796.9	65.6
0°-40°	1052.0	86.7
0°-60°	1192.4	98.2
0°-90°	1214.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1214.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1307	
5°	1290	121
15°	1138	316
25°	790	360
35°	406	255
45°	145	116
55°	18	25
65°	12	12
75°	7	7
85°	2	3
90°	0	

TEST NUMBER: P1265579

CATALOG NUMBER: P3AS17R609730DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1307.3
2.5°	1302.7
5°	1290.0
7.5°	1268.1
10°	1238.1
12.5°	1195.4
15°	1137.7
17.5°	1065.0
20°	979.6
22.5°	887.3
25°	790.4
27.5°	691.1
30°	591.9
32.5°	497.3
35°	406.2
37.5°	325.4
40°	252.7
42.5°	191.5
45°	145.4
47.5°	108.5
50°	71.5
52.5°	33.5
55°	18.5
57.5°	16.2
60°	15.0
62.5°	13.8
65°	11.5
67.5°	10.4
70°	9.2
72.5°	8.1
75°	6.9
77.5°	5.8
80°	4.6
82.5°	3.5
85°	2.3
87.5°	1.2
90°	0.0

(END OF REPORT)