

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265594

Luminaire Tested: P3AS17R609730DE010 E3DLP1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265594
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609730DE010 E3DLP1WMH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 97CRI , E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 840.0 lumens
Efficiency: N/A
Efficacy: 39.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265594

CATALOG NUMBER: P3AS17R609730DE010 E3DLP1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1265594

CATALOG NUMBER: P3AS17R609730DE010 E3DLP1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	212878
5°	208100
10°	194831
15°	174802
20°	150303
25°	124289
30°	98218
35°	72919
40°	50237
45°	31507
50°	17330
55°	10169
60°	9122
65°	7783
70°	6668
75°	6863
80°	5809
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 31507 cd/sqm

TEST NUMBER: P1265594

CATALOG NUMBER: P3AS17R609730DE010 E3DLP1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.0	10.5
10°-20°	213.8	25.5
20°-30°	234.5	27.9
30°-40°	170.9	20.3
40°-50°	80.7	9.6
50°-60°	26.5	3.2
60°-70°	15.0	1.8
70°-80°	8.1	1.0
80°-90°	2.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	536.4	63.9
0°-40°	707.3	84.2
0°-60°	814.5	97.0
0°-90°	840.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	840.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	971	
5°	945	88
15°	770	214
25°	514	235
35°	272	171
45°	102	81
55°	27	26
65°	15	15
75°	8	8
85°	2	3
90°	0	

TEST NUMBER: P1265594

CATALOG NUMBER: P3AS17R609730DE010 E3DLP1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	970.8
2.5°	965.0
5°	945.4
7.5°	915.4
10°	875.0
12.5°	826.5
15°	770.0
17.5°	708.8
20°	644.1
22.5°	578.3
25°	513.7
27.5°	449.0
30°	387.9
32.5°	329.0
35°	272.4
37.5°	221.6
40°	175.5
42.5°	135.1
45°	101.6
47.5°	73.9
50°	50.8
52.5°	33.5
55°	26.6
57.5°	23.1
60°	20.8
62.5°	17.3
65°	15.0
67.5°	12.7
70°	10.4
72.5°	9.2
75°	8.1
77.5°	5.8
80°	4.6
82.5°	3.5
85°	2.3
87.5°	1.2
90°	0.0

(END OF REPORT)