

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266406

Luminaire Tested: P3AS02R609735DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266406
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609735DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 272.0 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266406

CATALOG NUMBER: P3AS02R609735DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1266406

CATALOG NUMBER: P3AS02R609735DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	96	91	88	93	89	86	91	87	85	88	86	84	82		
4	98	91	85	81	96	90	85	81	88	83	80	86	82	79	84	81	78	77		
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72		
6	89	80	74	70	87	79	74	70	78	73	70	77	72	69	75	72	69	67		
7	85	76	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63		
8	81	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	61	59		
9	77	67	62	58	76	67	61	58	66	61	57	65	61	57	64	60	57	56		
10	73	64	58	54	72	63	58	54	63	58	54	62	57	54	61	57	54	53		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	71266
5°	67268
10°	65530
15°	64041
20°	59529
25°	53229
30°	40664
35°	23477
40°	9103
45°	3783
50°	819
55°	115
60°	88
65°	52
70°	64
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3783 cd/sqm

TEST NUMBER: P1266406

CATALOG NUMBER: P3AS02R609735DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.9	10.6
10°-20°	78.6	28.9
20°-30°	98.4	36.2
30°-40°	55.0	20.2
40°-50°	10.5	3.8
50°-60°	0.5	0.2
60°-70°	0.1	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	205.8	75.7
0°-40°	260.8	95.9
0°-60°	271.8	99.9
0°-90°	272.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	272.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	325	
5°	306	29
15°	282	79
25°	220	98
35°	88	55
45°	12	10
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1266406

CATALOG NUMBER: P3AS02R609735DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	325.0
1°	323.7
2°	319.4
3°	314.4
4°	309.8
5°	305.6
6°	302.5
7°	299.9
8°	297.9
9°	296.0
10°	294.3
11°	292.6
12°	290.7
13°	288.4
14°	285.6
15°	282.1
16°	277.7
17°	272.8
18°	267.3
19°	260.9
20°	255.1
21°	248.9
22°	242.4
23°	235.7
24°	228.2
25°	220.0
26°	210.3
27°	199.5
28°	187.4
29°	174.5
30°	160.6
31°	146.5
32°	132.1
32.5°	124.2
33°	117.1
34°	102.3
35°	87.7
36°	74.5
37°	60.6
37.5°	54.3
38°	48.1
39°	38.7
40°	31.8
42.5°	19.4
45°	12.2



TEST NUMBER: P1266406

CATALOG NUMBER: P3AS02R609735DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	6.8
50°	2.4
52.5°	0.6
55°	0.3
57.5°	0.2
60°	0.2
62.5°	0.1
65°	0.1
67.5°	0.1
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)