

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265596

Luminaire Tested: P3AS17R659730DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265596
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659730DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1428.0 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265596

CATALOG NUMBER: P3AS17R659730DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1265596

CATALOG NUMBER: P3AS17R659730DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	108	106	111	109	106	104	105	103	101		101	99	98		97
2	108	103	99	96	106	101	98	95	98	95	93		95	93	91		92
3	103	96	91	87	101	95	90	87	92	88	85		90	87	84		88
4	97	90	84	80	96	89	84	80	87	82	79		85	81	78		83
5	93	84	78	74	91	83	78	74	82	77	73		80	76	73		78
6	88	79	73	69	86	78	73	69	77	72	68		75	71	68		74
7	84	74	68	64	82	74	68	64	72	67	64		71	67	63		70
8	80	70	64	60	78	69	64	60	68	63	60		67	63	59		66
9	76	66	60	56	75	66	60	56	65	60	56		64	59	56		63
10	72	63	57	53	71	62	57	53	61	56	53		60	56	53		60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	348963
5°	328439
10°	324265
15°	318549
20°	300769
25°	279137
30°	216970
35°	125521
40°	50580
45°	23289
50°	9074
55°	3517
60°	3026
65°	3009
70°	2949
75°	2965
80°	2904
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 23289 cd/sqm

TEST NUMBER: P1265596

CATALOG NUMBER: P3AS17R659730DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.8	9.9
10°-20°	391.8	27.4
20°-30°	512.9	35.9
30°-40°	297.1	20.8
40°-50°	63.6	4.5
50°-60°	10.4	0.7
60°-70°	5.7	0.4
70°-80°	3.4	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1046.6	73.3
0°-40°	1343.7	94.1
0°-60°	1417.7	99.3
0°-90°	1428.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1428.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1591	
5°	1492	142
15°	1403	392
25°	1154	513
35°	469	297
45°	75	64
55°	9	10
65°	6	6
75°	4	3
85°	1	1
90°	0	

TEST NUMBER: P1265596

CATALOG NUMBER: P3AS17R659730DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	1591.4
2.5°	1546.4
5°	1492.1
7.5°	1470.2
10°	1456.3
12.5°	1436.7
15°	1403.2
17.5°	1351.2
20°	1288.9
22.5°	1230.0
25°	1153.7
27.5°	1025.5
30°	856.9
32.5°	664.1
35°	468.9
37.5°	296.8
40°	176.7
42.5°	110.9
45°	75.1
47.5°	48.5
50°	26.6
52.5°	12.7
55°	9.2
57.5°	8.1
60°	6.9
62.5°	6.9
65°	5.8
67.5°	4.6
70°	4.6
72.5°	3.5
75°	3.5
77.5°	2.3
80°	2.3
82.5°	1.2
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)