

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266417

Luminaire Tested: P3AS02R609735DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266417
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R609735DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 97CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 92.0 lumens
Efficiency: N/A
Efficacy: 25.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266417
CATALOG NUMBER: P3AS02R609735DE010 E3DLD1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1266417

CATALOG NUMBER: P3AS02R609735DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	16336
5°	16157
10°	15586
15°	14733
20°	13581
25°	12291
30°	10913
35°	9316
40°	7414
45°	5241
50°	3138
55°	1567
60°	1535
65°	1401
70°	1282
75°	1271
80°	1137
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5241 cd/sqm



TEST NUMBER: P1266417
 CATALOG NUMBER: P3AS02R609735DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.9	7.5
10°-20°	18.1	19.7
20°-30°	23.3	25.3
30°-40°	21.6	23.5
40°-50°	13.2	14.3
50°-60°	4.4	4.8
60°-70°	2.7	2.9
70°-80°	1.5	1.6
80°-90°	0.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	48.3	52.5
0°-40°	69.9	75.9
0°-60°	87.4	95.0
0°-90°	92.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	92.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	74	
5°	73	7
15°	65	18
25°	51	23
35°	35	22
45°	17	13
55°	4	4
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1266417
CATALOG NUMBER: P3AS02R609735DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	74.5
2.5°	74.1
5°	73.4
7.5°	71.9
10°	70.0
12.5°	67.7
15°	64.9
17.5°	61.6
20°	58.2
22.5°	54.5
25°	50.8
27.5°	47.0
30°	43.1
32.5°	39.2
35°	34.8
37.5°	30.3
40°	25.9
42.5°	21.3
45°	16.9
47.5°	13.1
50°	9.2
52.5°	5.5
55°	4.1
57.5°	3.8
60°	3.5
62.5°	3.0
65°	2.7
67.5°	2.3
70°	2.0
72.5°	1.7
75°	1.5
77.5°	1.1
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.2
90°	0.0

(END OF REPORT)