

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265618

Luminaire Tested: P3AS17R659730DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265618
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659730DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 97CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 392.0 lumens
Efficiency: N/A
Efficacy: 18.5 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 21.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265618

CATALOG NUMBER: P3AS17R659730DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265618

CATALOG NUMBER: P3AS17R659730DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		92
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		85
3	101	94	88	84	99	92	87	83	90	85	82		87	84	81		78
4	95	87	81	76	93	86	80	76	84	79	75		82	78	74		72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		66
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		62
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		57
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		54
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		50
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	99641
5°	97160
10°	90490
15°	81090
20°	70029
25°	58261
30°	45931
35°	34050
40°	23444
45°	14544
50°	7914
55°	4970
60°	4210
65°	3788
70°	3270
75°	2881
80°	2904
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14544 cd/sqm

TEST NUMBER: P1265618

CATALOG NUMBER: P3AS17R659730DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	41.0	10.5
10°-20°	99.3	25.3
20°-30°	109.8	28.0
30°-40°	79.7	20.3
40°-50°	37.3	9.5
50°-60°	12.6	3.2
60°-70°	7.3	1.9
70°-80°	3.8	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	250.0	63.8
0°-40°	329.8	84.1
0°-60°	379.7	96.9
0°-90°	392.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	392.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	454	
5°	441	41
15°	357	99
25°	241	110
35°	127	80
45°	47	37
55°	13	13
65°	7	7
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1265618

CATALOG NUMBER: P3AS17R659730DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	454.4
2.5°	451.6
5°	441.4
7.5°	426.1
10°	406.4
12.5°	383.2
15°	357.2
17.5°	328.9
20°	300.1
22.5°	270.1
25°	240.8
27.5°	210.8
30°	181.4
32.5°	153.2
35°	127.2
37.5°	103.4
40°	81.9
42.5°	62.7
45°	46.9
47.5°	33.9
50°	23.2
52.5°	15.8
55°	13.0
57.5°	11.3
60°	9.6
62.5°	8.5
65°	7.3
67.5°	6.2
70°	5.1
72.5°	4.5
75°	3.4
77.5°	2.8
80°	2.3
82.5°	1.7
85°	1.1
87.5°	0.6
90°	0.0

(END OF REPORT)