

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266478

Luminaire Tested: P3AS02R709735DE010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266478
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709735DE010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 163.0 lumens
Efficiency: N/A
Efficacy: 45.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266478

CATALOG NUMBER: P3AS02R709735DE010 E3DLP1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1266478

CATALOG NUMBER: P3AS02R709735DE010 E3DLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92		
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84		
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77		
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71		
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65		
6	85	75	68	64	83	74	68	63	73	67	63	71	66	63	70	65	62	61		
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56		
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52		
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49		
10	69	58	52	48	67	58	52	48	57	51	48	56	51	47	55	51	47	46		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	38243
5°	37530
10°	35381
15°	32123
20°	28096
25°	23687
30°	19395
35°	15044
40°	10763
45°	6822
50°	3411
55°	2064
60°	1798
65°	1660
70°	1475
75°	1356
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6822 cd/sqm

TEST NUMBER: P1266478

CATALOG NUMBER: P3AS02R709735DE010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.9	9.8
10°-20°	39.4	24.2
20°-30°	44.8	27.5
30°-40°	35.0	21.5
40°-50°	17.2	10.6
50°-60°	5.3	3.3
60°-70°	3.1	1.9
70°-80°	1.7	1.0
80°-90°	0.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	100.1	61.4
0°-40°	135.2	82.9
0°-60°	157.7	96.7
0°-90°	163.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	163.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	174	
5°	170	16
15°	142	39
25°	98	45
35°	56	35
45°	22	17
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1266478

CATALOG NUMBER: P3AS02R709735DE010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	174.4
2.5°	173.5
5°	170.5
7.5°	165.7
10°	158.9
12.5°	151.0
15°	141.5
17.5°	131.3
20°	120.4
22.5°	109.1
25°	97.9
27.5°	87.1
30°	76.6
32.5°	66.2
35°	56.2
37.5°	46.7
40°	37.6
42.5°	29.2
45°	22.0
47.5°	15.4
50°	10.0
52.5°	6.6
55°	5.4
57.5°	4.8
60°	4.1
62.5°	3.6
65°	3.2
67.5°	2.7
70°	2.3
72.5°	1.8
75°	1.6
77.5°	1.4
80°	0.9
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)