

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266479

Luminaire Tested: P3AS02R709735DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266479
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS02R709735DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 97CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 229.0 lumens
Efficiency: N/A
Efficacy: 63.6 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 3.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266479

CATALOG NUMBER: P3AS02R709735DE010 E3DLP1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1266479

CATALOG NUMBER: P3AS02R709735DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	96	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	82	89	85	81		86	83	80		84
4	94	86	80	75	93	85	79	75	83	78	74		81	76	73		79
5	89	80	73	69	87	79	73	68	77	72	68		75	71	67		74
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	53	74	64	58	53	63	57	53		62	57	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	50	46	66	56	50	46	55	50	46		55	49	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44339
5°	43804
10°	42529
15°	40727
20°	38153
25°	34671
30°	29954
35°	23851
40°	17375
45°	11412
50°	5356
55°	1644
60°	1579
65°	1557
70°	1475
75°	1525
80°	1389
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11412 cd/sqm

TEST NUMBER: P1266479

CATALOG NUMBER: P3AS02R709735DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	18.7	8.2
10°-20°	50.2	21.9
20°-30°	65.3	28.5
30°-40°	55.4	24.2
40°-50°	28.6	12.5
50°-60°	5.5	2.4
60°-70°	3.0	1.3
70°-80°	1.8	0.8
80°-90°	0.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	134.2	58.6
0°-40°	189.6	82.8
0°-60°	223.7	97.7
0°-90°	229.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	229.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	202	
5°	199	19
15°	179	50
25°	143	65
35°	89	55
45°	37	29
55°	4	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1266479

CATALOG NUMBER: P3AS02R709735DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	202.2
2.5°	201.5
5°	199.0
7.5°	195.3
10°	191.0
12.5°	185.6
15°	179.4
17.5°	171.9
20°	163.5
22.5°	154.0
25°	143.3
27.5°	131.2
30°	118.3
32.5°	103.9
35°	89.1
37.5°	74.6
40°	60.7
42.5°	47.8
45°	36.8
47.5°	27.1
50°	15.7
52.5°	6.8
55°	4.3
57.5°	4.1
60°	3.6
62.5°	3.4
65°	3.0
67.5°	2.7
70°	2.3
72.5°	2.0
75°	1.8
77.5°	1.4
80°	1.1
82.5°	0.7
85°	0.5
87.5°	0.2
90°	0.0

(END OF REPORT)