

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265693

Luminaire Tested: P3AS20R159730D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R159730D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 771.0 lumens
Efficiency: N/A
Efficacy: 26.8 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265693

CATALOG NUMBER: P3AS20R159730D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265693

CATALOG NUMBER: P3AS20R159730D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	658631
5°	584634
10°	406005
15°	240115
20°	136745
25°	78174
30°	43247
35°	23075
40°	12767
45°	6915
50°	4298
55°	3403
60°	2938
65°	2698
70°	2372
75°	2542
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6915 cd/sqm

TEST NUMBER: P1265693

CATALOG NUMBER: P3AS20R159730D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.9	29.3
10°-20°	298.1	38.7
20°-30°	153.5	19.9
30°-40°	57.6	7.5
40°-50°	18.9	2.4
50°-60°	8.1	1.1
60°-70°	5.1	0.7
70°-80°	3.0	0.4
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	677.4	87.9
0°-40°	735.0	95.3
0°-60°	762.0	98.8
0°-90°	771.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	771.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3004	
5°	2656	226
15°	1058	298
25°	323	153
35°	86	58
45°	22	19
55°	9	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1265693

CATALOG NUMBER: P3AS20R159730D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	3003.6
1°	2997.7
2°	2958.3
3°	2883.3
4°	2784.5
5°	2656.0
6°	2510.4
7°	2350.8
8°	2173.2
9°	1998.0
10°	1823.4
12.5°	1403.0
15°	1057.7
17.5°	791.8
20°	586.0
22.5°	437.5
25°	323.1
27.5°	235.4
30°	170.8
32.5°	121.1
35°	86.2
37.5°	61.6
40°	44.6
42.5°	31.9
45°	22.3
47.5°	16.3
50°	12.6
52.5°	10.4
55°	8.9
57.5°	7.4
60°	6.7
62.5°	5.9
65°	5.2
67.5°	4.5
70°	3.7
72.5°	3.7
75°	3.0
77.5°	2.2
80°	1.5
82.5°	1.5
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)