

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1266537

Luminaire Tested: P3AS05R129735DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1266537
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R129735DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R12 optic, 3500K CCT AND, 97CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 471.0 lumens
Efficiency: N/A
Efficacy: 62.0 lumens/watt
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1266537

CATALOG NUMBER: P3AS05R129735DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1266537

CATALOG NUMBER: P3AS05R129735DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	106	103	100	108	104	101	99	101	99	97		98	96	95		96
3	106	101	97	93	104	99	96	93	97	94	91		94	92	90		92
4	102	96	92	88	100	95	91	88	93	89	87		91	88	86		89
5	98	92	87	84	97	91	87	83	89	85	83		88	84	82		86
6	95	88	83	80	94	87	83	80	86	82	79		85	81	79		83
7	92	85	80	77	91	84	80	76	83	79	76		82	78	76		81
8	89	81	77	74	88	81	77	73	80	76	73		79	75	73		78
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76
10	84	76	71	68	83	76	71	68	75	71	68		74	71	68		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	402358
5°	357164
10°	248025
15°	146675
20°	83541
25°	47761
30°	26434
35°	14081
40°	7786
45°	4217
50°	2627
55°	2064
60°	1798
65°	1660
70°	1475
75°	1525
80°	1137
85°	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 4217 cd/sqm

TEST NUMBER: P1266537

CATALOG NUMBER: P3AS05R129735DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.0	29.3
10°-20°	182.1	38.7
20°-30°	93.8	19.9
30°-40°	35.2	7.5
40°-50°	11.5	2.4
50°-60°	4.9	1.1
60°-70°	3.1	0.7
70°-80°	1.9	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	413.8	87.9
0°-40°	449.0	95.3
0°-60°	465.5	98.8
0°-90°	471.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	471.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1835	
5°	1623	138
15°	646	182
25°	197	94
35°	53	35
45°	14	12
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	

TEST NUMBER: P1266537

CATALOG NUMBER: P3AS05R129735DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1834.9
1°	1831.3
2°	1807.2
3°	1761.4
4°	1701.0
5°	1622.6
6°	1533.6
7°	1436.1
8°	1327.6
9°	1220.5
10°	1113.9
12.5°	857.1
15°	646.1
17.5°	483.7
20°	358.0
22.5°	267.2
25°	197.4
27.5°	143.8
30°	104.4
32.5°	74.0
35°	52.6
37.5°	37.7
40°	27.2
42.5°	19.5
45°	13.6
47.5°	10.0
50°	7.7
52.5°	6.4
55°	5.4
57.5°	4.5
60°	4.1
62.5°	3.6
65°	3.2
67.5°	2.7
70°	2.3
72.5°	2.3
75°	1.8
77.5°	1.4
80°	0.9
82.5°	0.9
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)