

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265714

Luminaire Tested: P3AS20R209730D010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265714
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209730D010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1913.9 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265714
CATALOG NUMBER: P3AS20R209730D010 E3CB1MB

Luminous Intensity Polar Plot





TEST NUMBER: P1265714
 CATALOG NUMBER: P3AS20R209730D010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98	98	98	98
2	112	109	107	104	110	108	105	103	104	103	101	102	100	99	99	98	97	97	98	97	95
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	95	97	96	93
4	107	102	99	96	105	101	98	96	99	97	95	97	95	93	96	94	92	96	94	92	91
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	94	92	91	90
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	93	90	89	88
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	91	89	87	86
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	89	87	85	85
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	88	86	84	83
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	87	84	82	87	84	82	82

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2972657
5°	2580161
10°	1594270
15°	553738
20°	170045
25°	60124
30°	22257
35°	8914
40°	4780
45°	1892
50°	1023
55°	1147
60°	1316
65°	778
70°	962
75°	1271
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1892 cd/sqm



TEST NUMBER: P1265714
 CATALOG NUMBER: P3AS20R209730D010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	972.8	50.8
10°-20°	771.9	40.3
20°-30°	133.6	7.0
30°-40°	24.3	1.3
40°-50°	5.6	0.3
50°-60°	2.7	0.1
60°-70°	1.7	0.1
70°-80°	1.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1878.3	98.1
0°-40°	1902.6	99.4
0°-60°	1910.9	99.8
0°-90°	1913.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1913.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13556	
5°	11722	973
15°	2439	772
25°	248	134
35°	33	24
45°	6	6
55°	3	3
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1265714
CATALOG NUMBER: P3AS20R209730D010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	13556.4
1°	13491.3
2°	13233.7
3°	12820.1
4°	12335.3
5°	11721.7
6°	11018.8
7°	10200.6
8°	9268.9
9°	8222.0
10°	7160.0
12.5°	4516.3
15°	2439.2
17.5°	1302.9
20°	728.7
22.5°	416.6
25°	248.5
27.5°	151.5
30°	87.9
32.5°	51.5
35°	33.3
37.5°	22.7
40°	16.7
42.5°	10.6
45°	6.1
47.5°	3.0
50°	3.0
52.5°	3.0
55°	3.0
57.5°	3.0
60°	3.0
62.5°	1.5
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	1.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)