

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265739

Luminaire Tested: P3AS20R209730D010 E3PHLP1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265739
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209730D010 E3PHLP1MW
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 97CRI , E3PHLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 742.0 lumens
Efficiency: N/A
Efficacy: 25.8 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265739
CATALOG NUMBER: P3AS20R209730D010 E3PHLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1265739
 CATALOG NUMBER: P3AS20R209730D010 E3PHLP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	95	95	93	92	90			90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74			74
4	93	84	78	73	91	83	77	73	81	76	72	79	74	71	77	73	70	68			68
5	88	79	72	67	86	78	71	67	76	70	66	74	69	66	72	68	65	63			63
6	84	74	67	62	82	73	66	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	63	58	78	68	62	58	67	62	57	66	61	57	65	60	57	55			55
8	76	65	59	54	74	65	58	54	64	58	54	62	57	54	61	57	53	52			52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49			49
10	69	59	52	48	68	58	52	48	57	52	48	57	52	48	56	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	263860
5°	246114
10°	204227
15°	156164
20°	117214
25°	88239
30°	65251
35°	45588
40°	31259
45°	21677
50°	18626
55°	18351
60°	19165
65°	19250
70°	19619
75°	20334
80°	22099
85°	21889

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 82.5°
 Luminance: 25704 cd/sqm



TEST NUMBER: P1265739
 CATALOG NUMBER: P3AS20R209730D010 E3PHLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.2	13.5
10°-20°	191.3	25.8
20°-30°	168.3	22.7
30°-40°	108.6	14.6
40°-50°	57.6	7.8
50°-60°	43.3	5.8
60°-70°	36.8	5.0
70°-80°	25.9	3.5
80°-90°	10.1	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	459.7	62.0
0°-40°	568.3	76.6
0°-60°	669.2	90.2
0°-90°	742.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	742.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1203	
5°	1118	100
15°	688	191
25°	365	168
35°	170	109
45°	70	58
55°	48	43
65°	37	37
75°	24	26
85°	9	10
90°	0	



TEST NUMBER: P1265739
CATALOG NUMBER: P3AS20R209730D010 E3PHLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1203.3
2.5°	1179.3
5°	1118.1
7.5°	1024.2
10°	917.2
12.5°	799.3
15°	687.9
17.5°	587.5
20°	502.3
22.5°	430.2
25°	364.7
27.5°	307.9
30°	257.7
32.5°	211.8
35°	170.3
37.5°	137.6
40°	109.2
42.5°	87.4
45°	69.9
47.5°	61.1
50°	54.6
52.5°	50.2
55°	48.0
57.5°	45.9
60°	43.7
62.5°	39.3
65°	37.1
67.5°	34.9
70°	30.6
72.5°	28.4
75°	24.0
77.5°	21.8
80°	17.5
82.5°	15.3
85°	8.7
87.5°	4.4
90°	0.0

(END OF REPORT)