

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265776

Luminaire Tested: P3AS20R309730D010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265776
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309730D010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1928.9 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265776

CATALOG NUMBER: P3AS20R309730D010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1265776

CATALOG NUMBER: P3AS20R309730D010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	93	92
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	91	90	89
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	88	87	86
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	87	86	85	84
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	83	82	81
7	96	90	86	83	95	89	86	83	88	85	83	87	84	82	86	84	82	81	80	79
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	78	77
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	76	75	74
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	77	75	74	73	72

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1570861
5°	1541180
10°	1364326
15°	864386
20°	328119
25°	97143
30°	38360
35°	11752
40°	5210
45°	1892
50°	1535
55°	1147
60°	1316
65°	1557
70°	962
75°	1271
80°	1894
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 80°
Luminance: 1894 cd/sqm

TEST NUMBER: P1265776

CATALOG NUMBER: P3AS20R309730D010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	643.6	33.4
10°-20°	1003.1	52.0
20°-30°	232.9	12.1
30°-40°	36.1	1.9
40°-50°	6.2	0.3
50°-60°	2.9	0.1
60°-70°	2.4	0.1
70°-80°	1.6	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1879.6	97.4
0°-40°	1915.7	99.3
0°-60°	1924.7	99.8
0°-90°	1928.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1928.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7164	
5°	7002	644
15°	3808	1003
25°	402	233
35°	44	36
45°	6	6
55°	3	3
65°	3	2
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1265776

CATALOG NUMBER: P3AS20R309730D010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	7163.7
1°	7159.1
2°	7139.4
3°	7106.1
4°	7063.7
5°	7001.6
6°	6924.3
7°	6809.1
8°	6651.6
9°	6419.7
10°	6127.3
11°	5750.0
12°	5324.3
13°	4851.5
14°	4331.8
15°	3807.6
17.5°	2490.9
20°	1406.1
22.5°	718.2
25°	401.5
27.5°	247.0
30°	151.5
32.5°	81.8
35°	43.9
37.5°	28.8
40°	18.2
42.5°	10.6
45°	6.1
47.5°	4.5
50°	4.5
52.5°	3.0
55°	3.0
57.5°	3.0
60°	3.0
62.5°	3.0
65°	3.0
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	1.5
80°	1.5
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1265776

CATALOG NUMBER: P3AS20R309730D010 E3CD1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)