

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1265783

Luminaire Tested: P3AS20R309730D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1265783
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309730D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3000K CCT AND, 97CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 786.9 lumens
Efficiency: N/A
Efficacy: 27.3 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1265783

CATALOG NUMBER: P3AS20R309730D010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1265783

CATALOG NUMBER: P3AS20R309730D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		79
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	459240
5°	437111
10°	367662
15°	265155
20°	164468
25°	93538
30°	51957
35°	28268
40°	14885
45°	8063
50°	4298
55°	2829
60°	2588
65°	2698
70°	2372
75°	1864
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8063 cd/sqm

TEST NUMBER: P1265783

CATALOG NUMBER: P3AS20R309730D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	178.8	22.7
10°-20°	317.8	40.4
20°-30°	183.7	23.3
30°-40°	69.7	8.9
40°-50°	21.4	2.7
50°-60°	7.2	0.9
60°-70°	4.9	0.6
70°-80°	2.6	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	680.3	86.5
0°-40°	750.1	95.3
0°-60°	778.6	98.9
0°-90°	786.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	786.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2094	
5°	1986	179
15°	1168	318
25°	387	184
35°	106	70
45°	26	21
55°	7	7
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1265783

CATALOG NUMBER: P3AS20R309730D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2094.3
1°	2092.8
2°	2080.2
3°	2056.4
4°	2026.6
5°	1985.8
6°	1933.7
7°	1875.7
8°	1811.0
9°	1733.7
10°	1651.2
11°	1562.0
12°	1467.6
13°	1368.7
14°	1268.3
15°	1168.0
17.5°	921.1
20°	704.8
22.5°	522.6
25°	386.6
27.5°	281.0
30°	205.2
32.5°	147.9
35°	105.6
37.5°	73.6
40°	52.0
42.5°	36.4
45°	26.0
47.5°	17.8
50°	12.6
52.5°	8.9
55°	7.4
57.5°	6.7
60°	5.9
62.5°	5.2
65°	5.2
67.5°	4.5
70°	3.7
72.5°	3.0
75°	2.2
77.5°	2.2
80°	1.5
82.5°	1.5
85°	0.7
87.5°	0.0



TEST NUMBER: P1265783

CATALOG NUMBER: P3AS20R309730D010 E3DL1GPH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)